

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022013037

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 3 Circuits

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	2695
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753593831
Physical	
Circuits (maximum)	3
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.320/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	2695-03RP
Reference - Drawing Numbers	
Sales Drawing	SD-2695



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

2695 Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION