

High Value Multilayer Ceramic Capacitors (High dielectric type)

UMK325BJ106MM-T



■ Features

- Item Summary
10uF±20%, 50V,
X5R, 1210/3225 (EIA/JIS)
- Lifecycle Stage
Non-preferred
- Standard packaging quantity (minimum)
Taping Embossed 500pcs

■ Products characteristics table

Capacitance	10 uF ± 20 %
Case Size (EIA/JIS)	1210/3225
Rated Voltage	50 V
tan δ (max)	5 %
Temperature Characteristic (EIA)	X5R
Operating Temp. Range (EIA)	-55 to +85 °C
HALT (% Rated Voltage)	150 %
Insulation Resistance (min)	100 MΩ · μF
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 ± 0.30 mm
Dimension W	2.5 ± 0.20 mm
Dimension T	2.5 ± 0.20 mm
Dimension e	0.60 ± 0.30 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.