



Datasheet for part number 192993-0014

| |
|---|
| Our Catalog Part Number: TNM6S16-0019P1L |
| Our Global Manufacturing Part Number: 192993-0014 |
| Brand: Cannon Product Category: Trident Product Line: Trident Series: TNM |

| | |
|---------------------------|---|
| Product Datasheet | |
| Series | Trident Neptune Metal |
| Operating Voltage | Up to 250 V ac rms |
| Contact Current Rating | Up to 13 A Up to 16 A with High Conductivity Contacts Up to 30 A with High Power Contacts |
| Operating Temperature | -55°C to +105°C |
| Insulation Resistance | 5000 Megaohms at 500 V dc |
| Durability | Up to 200 Mating Cycles |
| Sealing | Up to IP67 |
| Flammability Rating | UL94-V0 |
| Materials and Finishes | Shell: Nickel Plated Zinc Alloy Insulator: Nylon Coupling Ring: Nickel Plated Brass Seal: Rubber |
| Shell Style | Plug |
| Sealing Class | Sealed: With Grommet and nut |
| Shell Size | 16 |
| Number of Power Contacts | 00 |
| Number of Contacts | 19 |
| Contact Style | Pin |
| Connector Finish/Material | Standard (Nickel Plated Metal Parts) |
| Packaging | Single Pack |
| Modification Code | Standard part |