

# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Precision wire strippers
<b>Catalogue number</b>	3576, 3755, 3757ESD, 3757 & 3759
<b>Date</b>	27/03/2015

## Range Description

A range of precision wire strippers

## Features

- Compact design – convenient to carry
- Precision wire stripping – damage free wire preparation every time
- Depth stop adjustable up to 50mm with 1mm graduations – accurate and repeatable wire stripping
- Specially hardened blades – for a long life
- ESD version available for ESD safe areas



3756



3755



3757ESD



T3757 (330013)



3759 (330012)

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3755 060	Precision Fibre optic wire stripper 0.60mm Diameter Cable	5013969489804	82032000	1
T3755 018	Precision Fibre optic wire stripper for 0.18mm Diameter Cable	5013969489507	82032000	1
T3756 20	Precision wire stripper for 0.2mm Diameter Wire	5013969497809	82032000	1
T3756 25	Precision wire stripper for 0.25mm Diameter Wire	5013969497908	82032000	1
T3756 30	Precision wire stripper for 0.3mm Diameter Wire	5013969498004	82032000	1
T3756 40	Precision wire stripper for 0.4mm Diameter Wire	5013969498103	82032000	1
T3756 50	Precision wire stripper for 0.5mm Diameter Wire	5013969498202	82032000	1
T3756 60	Precision wire stripper for 0.6mm Diameter Wire	5013969498301	82032000	1
T3756 80	Precision wire stripper for 0.8mm Diameter Wire	5013969498400	82032000	1
T3756 100	Precision wire stripper for 1.0mm Diameter Wire	5013969497700	82032000	1
T3757ESD 1	Precision wire stripper for 0.12 to 0.4mm Diameter Wire	5013969020441	82032000	1
T3757ESD 2	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5013969020434	82032000	1
T3757ESD 3	Precision wire stripper for 0.3 to 1.0mm Diameter Wire	5013969020458	82032000	1
330009	Precision wire stripper 0.12 to 0.4mm Diameter Wire	5051073300097	82032000	1
330011	Precision wire stripper 0.3 to 1.0mm Diameter Wire	5051073300110	82032000	1
330012	Precision wire stripper 0.25 to 0.8mm Diameter Wire	5051073300127	82032000	1
330013	Precision wire stripper for 0.25 to 0.8mm Diameter Wire	5051073300103	82032000	1
Z3757 1	Set of replacement blades for 330009	5013969781304	82032000	6
Z3757 2	Set of replacement blades for 330013	5013969783506	82032000	6
Z3757 3	Set of replacement blades for 330011	5013969783704	82032000	6

Technical product information

**Wire types**  
For PVC, Teflon and similar coated wires

**Wire stripping capacities**

T3755	mm	0.18						
	awg	33						
T3755 060	mm	0.6						
	awg	22						
T3756 20	mm	0.2						
	awg	32						
T3756 25	mm	0.25						
	awg	30						
T3756 30	mm	0.3						
	awg	28						
T3756 40	mm	0.4						
	awg	26						
T3756 50	mm	0.5						
	awg	24						
T3756 60	mm	0.6						
	awg	22						
T3756 80	mm	0.8						
	awg	20						
T3756 100	mm	1						
	awg	18						
T3757ESD 1	mm	0.12	0.16	0.20	0.25	0.30	0.40	
	awg	36	34	32	30	28	26	
T3757ESD 2	mm	0.25	0.3	0.4	0.5	0.6	0.8	
	awg	30	28	26	24	22	20	
T3757ESD 3	mm	0.3	0.4	0.5	0.6	0.8	1	
	awg	28	26	24	22	20	18	
330009	mm	0.12	0.16	0.2	0.25	0.3	0.4	
	awg	36	34	32	30	28	26	
330011	mm	0.3	0.4	0.5	0.6	0.8	1	
	awg	28	26	24	22	20	18	
330012	mm	0.25	0.3	0.4	0.5	0.6	0.8	
	awg	30	28	26	24	22	20	
330013	mm	0.25	0.3	0.4	0.5	0.6	0.8	
	awg	30	28	26	24	22	20	

Standards compliance None applicable

User health and None applicable

safety information	
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Germany

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3755 018	98	10	54	26	98	10	54	27
T3755 060	98	15	45	20	98	15	45	21
T3756 20	98	10	54	24	98	10	54	25
T3756 25	98	10	54	24	98	10	54	25
T3756 30	98	10	54	24	98	10	54	25
T3756 40	98	10	54	24	98	10	54	25
T3756 50	98	10	54	24	98	10	54	25
T3756 60	98	10	54	24	98	10	54	25
T3756 80	98	10	54	24	98	10	54	25
T3756 100	98	10	54	24	98	10	54	25
T3757ESD 1	98	15	45	20	98	15	45	21
T3757ESD 2	98	10	54	26	98	10	54	27
T3757ESD 3	98	15	45	20	98	15	45	21
330009	98	10	54	26	98	10	54	27
330011	98	10	54	26	98	10	54	27
330012	100	11	40	30	100	11	40	31
330013	98	10	54	26	98	10	54	27
Z3757 1	7	5	1	9	55	55	1	10
Z3757 2	7	5	1	9	55	55	1	10
Z3757 3	7	5	1	9	55	55	1	10

## Packaging waste details

Primary Packaging	Secondary packaging
-------------------	---------------------

Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3755 018	1	Bag						
T3755 060	1	Bag						
T3756 20	1	Bag						
T3756 25	1	Bag						
T3756 30	1	Bag						
T3756 40	1	Bag						
T3756 50	1	Bag						
T3756 60	1	Bag						
T3756 80	1	Bag						
T3756 100	1	Bag						
T3757ESD 1	1	Bag						
T3757ESD 2	1	Bag						
T3757ESD 3	1	Bag						
330009	1	Bag						
330011	1	Bag						
330012	1	Bag						
330013	1	Bag						
Z3757 1	1	Bag						
Z3757 2	1	Bag						
Z3757 3	1	Bag						