



**Standard
T&B Catalog Number:**

TY524MX

UPC Number:

78621080699

Status:

Active

Description:

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 139.7mm (5.5 Inches), Width of 3.56mm (0.14 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 135 Newtons (30 Pounds), Military Specified (MIL-SPEC MS3367-5-0)

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material Nylon 6.6 Weather Resistant
Color Black

Dimension Information

Nominal Length (inches) 6
Length (inches) 5.5
Width (inches) .140
Max. Wire Bundle Diameter (inches) 1.125

Specifications

Military Standard Part No. MS3367-5
Temperature Rating -40°F to 185°F
Flammability Rating UL 94 V-2

Tooling

Application Tools ERG50, WT1-TB

Packaging

T&B Order Multiple 100
T&B Inner Pack 100
Package in Units 1000
Package Type Regular
T&B Sold in UOM Each
T&B Weight Per UOM 1.25 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com