



Standard
T&B Catalog Number:

TY527MX
78621080512
Active

UPC Number:
Status:
Description:

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 340.4mm (13.4 Inches), Width of 7.0mm (0.27 Inches), Thickness of 1.65mm (0.06 Inches), Tensile Strength Rating of 530 Newtons (120 Pounds), Military Specified (MIL-SPEC MS3367-3-0)

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	13
Length (inches)	13.4
Width (inches)	.270
Max. Wire Bundle Diameter (inches)	3.5

Specifications

Military Standard Part No.	MS3367-3
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG120, WT197
-------------------	---------------

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	1 lbs. per 100

Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
UL recognised	Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com