

**Flag Terminal
T&B Catalog Number:**

AB14-8A
78621080311
Active

**UPC Number:
Status:
Description:**


Non-Insulated Flag Terminal, Length .55 Inches, Width .31 Inches, Bolt Hole #8, Wire Range #22-#14 AWG, Copper, Tin Plated

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Flag terminals allow a 90 degree connection to the terminal block without bending the wire.



General

Insulation Type	Non-Insulated
Terminal Series	AB
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	22-14
Stud Size	#8

Dimension Information

Stock Thickness	.03
A (inches)	.55
B (inches)	.31
C (inches)	.22
M (inches)	.39

Specifications

Temperature Rating	150°C
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	ERG4004
Recommended Tool	ERG4004

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.25 lbs. per 100
Alternate Package Qty	AB52

Application Support

T&B Sales Drawings	wsd-001360
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com