

## Type B Liquidtight Tubing & Fittings

### T&B Catalog Number:

**UPC Number:**

EFC125

**Status:**

78621078964

**Description:**

Active

1-1/4 Inch Black Corrugated PVC Flexible Tubing

#### Features

Maximum flexibility in tight applications.

Extremely fast installation

Liquidtight with specified fittings.

Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

#### Application

Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship-board wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

#### General

Material

PVC

Color

Black

Working Temperatures

-18 C to +60 C

#### Dimension Information

Size (inches)

1 1/4

I.D. - Minimum (inches)

1.38

I.D. - Maximum (inches)

1.41

O.D. - Minimum (inches)

1.63

O.D. - Maximum (inches)

1.66

#### Packaging

T&B Order Multiple

100

Package in Units

100

T&B Sold in UOM

Feet

T&B Weight Per UOM

21.38 lbs. per 100

#### Application Support

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications

Available on Website

#### Certifications

RoHS Compliance

Yes

#### Certifications



File Nbr:

E 96548

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)