

Product data sheet

Characteristics

DZ5CE007

Cable end insulated, 0,75mm², medium size, blue,
10 bags, NF

Product availability: Stock - Normally stocked in distribution facility
Price*: 0.18 USD

Main

Range of productrange of product	Linergy
Product or component typeproduct or component type	Cable end
Cable end sizecable end size	Medium
Standardsstandards	NF C 63-023
Type of packingtype of packing	String of bags
Quantity per setquantity per set	10 sets of 100
Cable cross sectioncable cross section	0 in ² (0.75 mm ²)

Complementary

Cable end typecable end type	Single conductor
Additional informationadditional information	Without marker tag holder
Colorcolor	Blue
Bezel materialbezel material	Halogen-free plastic
Tube materialtube material	Copper conforming to ISO 1337
Number of cablesnumber of cables	1
AWG gaugeAWG gauge	AWG 20
Bezel sizebezel size	Ø 3.3 mm
Tube diametertube diameter	0.06 in (1.5 mm)
Lengthlength	0.55 in (14 mm)
Tube lengthtube length	0.31 in (8 mm)
CAD overall widthCAD overall width	0.12 in (3 mm)
CAD overall heightCAD overall height	0.12 in (3 mm)
CAD overall depthCAD overall depth	0.55 in (14 mm)
Product weightproduct weight	0.22 lb(US) (0.1 kg)

Environment

Product certificationsproduct certifications	UL
Ambient air temperature for operationambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

CategoryCategory	22621 - IEC PANEL ACCESSORIES
Discount ScheduleDiscount Schedule	I
GTINGTIN	00785901223092
Nbr. of units in pkg.Nbr. of units in pkg.	1000
ReturnabilityReturnability	Y
Country of originCountry of origin	DE

Offer Sustainability

Sustainable offer status	Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	RoHS (date code: YY-WW)	Compliant since 0437; Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	REACH	Reference not containing SVHC above the threshold
Product environmental profile	Product environmental profile	Available
Product end of life instructions	Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	Warranty period	18 months
-----------------	-----------------	-----------