

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192050009

Status:

Active

Overview:

[Splices](#)

Description:

VersaKrimp™ Parallel Splice for 1/0 AWG Wire

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

|                                |                         |
|--------------------------------|-------------------------|
| Agency Certification           |                         |
| CSA                            | LR18689                 |
| UL                             | E32244                  |
| General                        |                         |
| Product Family                 | Splices                 |
| Series                         | <a href="#">19205</a>   |
| Crimp Quality Equipment        | Yes                     |
| Mil-Spec                       | N/A                     |
| Overview                       | <a href="#">Splices</a> |
| Product Name                   | Parallel, VersaKrimp™   |
| UPC                            | 800755060881            |
| Physical                       |                         |
| Barrel Type                    | Closed - Brazed         |
| Insulation                     | None                    |
| Material - Metal               | Copper                  |
| Material - Plating Mating      | Tin                     |
| Material - Plating Termination | Tin                     |
| Net Weight                     | 13.336/g                |
| Packaging Type                 | Bag                     |
| Wire Size AWG                  | 1/0                     |
| Material Info                  |                         |
| Old Part Number                | H-384                   |
| Reference - Drawing Numbers    |                         |
| Sales Drawing                  | SD-19205-007            |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Not Relevant

Need more information on product

environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[19205](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

| Description         | Product #                  |
|---------------------|----------------------------|
| Hydraulic Dieless   | <a href="#">0638161700</a> |
| Crimping Tool       |                            |
| Manual tool for     | <a href="#">0192940008</a> |
| Crimping non-       |                            |
| insulated 8AWG thru |                            |
| 4/0 Terminals       |                            |
| Manual Putt Pump    | <a href="#">0192860117</a> |
| Hydraulic System,   |                            |
| Die set required    |                            |

Die Set (large) for 0192900011  
the HHLS Hydraulic  
Crimper

This document was generated on 07/28/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**