



7	6	5	4	3	2	1	
ECN NO.		REV	DESCRIPTION		DATE	REVISER	APPROVED

PIN ASSIGNMENT:

P2	P1	P3
1	1	1
2	2	2
3	3	3
4	4	4
5	5	5
6	6	6
7	7	7
8	8	8
9	9	9
10	10	10
11	11	11
12	12	12
13	13	13
14	14	14
15	15	15
SHELL	SHELL	SHELL

TABLE 1

PART NO.:	LENGTH(L)
	250±10

ELECTRICAL CHARACTER:
1.100% OPEN & SHORT TESTING.

GENERAL TOLERANCES (UNLESS SPECIFIED)	CUST PART NO.:
---------------------------------------	----------------

6	PVC: BEIGE WHITE.	g	18
5	PE: LD-PE.	g	15
4	SCREW: NICKEL PLATED.	PCS	6
3	CONN: DB 15P F, CONTACT: TINNED PLATED, SHELL: NICKEL PLATED, BLUE INSULATOR.	PCS	2
2	CONN: DB 15P M, CONTACT: GOLD PLATED, SHELL: NICKEL PLATED, BLUE INSULATOR.	PCS	1
1	CABLE: 30AWGx15C, OD: 5.5 PVC JACKET, BEIGE WHITE.	mm	SEE TABLE 1
ITEM	DESCRIPTION	UNIT	QTY

.XXX: ±0.15	ANGULAR: ±3°	DESIGN:	SCALE: NONE	UNIT: mm	THIRD ANGLE PROJECTION
.XX: ±0.25		CHECKED:	TITLE:		
.X: ±0.50		APPROVED:	PART NO.: SPLITTER LEAD 0.25M	REV: A	
DATE: 2016.08.03		SHEET NO.: 1 OF 1			