


#### **TFP SIDE-MOUNT**



#### **INDUSTRY STANDARDS**

UL 508A Component Recognized; File No. E61997 TFP# Models: Type 1 TFP# UL 12 Models: Type 12


CSA certified (fan only) CE

#### **APPLICATION**

- Industrial automation
- Automotive assembly
- Package handling equipment
- Food and beverage process controlls
- Wind energy systems

#### FEATURES

- Cooling Fan Package includes fan, air filter, composite air plenum, finger guard and grille
- Exhaust Package includes air filter, filter retainer with integral finger guard and grille
- EMC Upgrade Kit includes a grille standoff collar and a special EMC shielding grille
- Reliable cooling for enclosures with limited space requiring simple filtered airflow for basic cooling
- 24 VDC, 115 VAC and 230 VAC options available
- Washable foam (Type 1) or disposable (Type 12) filter in fan
- Dynamically-balanced fan impellers molded from polycarbonate material



- 4-in. fan is thermally protected and uses permanently-lubricated ball bearings
- 6- and 10-in. fans have ball bearing construction and splitcapacitor motors that are thermally protected to avoid premature failure
- Fans have lead wires for power connection with ends stripped 1/2 in. (12 mm)
- All mounting hardware and installation instructions are furnished

#### SPECIFICATIONS

- Free airflow from 45 CFM (76 m<sup>3</sup>/hr.) to 215 CFM (365 m<sup>3</sup>/hr.)
- Maximum operating temperature 158 F / 70 C
- Engineered for 50,000 hours of continuous operation without lubrication or service (a monthly maintenance schedule is recommended to ensure optimal cooling performance)

#### FINISH

- Stainless steel grilles have brushed finish.
- ABS composite grille is black.

#### ACCESSORIES

Aluminum Type 1 and Hi-Density Type 12 Filters

EMC Upgrade Kit Grille Options:


- Stainless Steel
- Black ABS Plastic




## Performance Data **TFP4 Models**

Rated Voltage	24 VDC	115 VAC	230 VAC
Frequency (Hz)		50/60	
Nominal Current Maximum @ 50/60 Hz(Amps)	.35	.26/.21	.14/.11
Power Consumption Maximum @ 50/60 Hz (Watts)	8.4	17/15	16/14
Power Connection	Stripped Leadwires		
CATALOG NUMBERS			
Composite Type 1			
Catalog Number	TFP424	TFP41	TFP42
Stainless Steel Type 1			
Catalog Number	_	TFP41SS	TFP42SS
Composite Type 12			
Catalog Number	_	TFP41UL12	TFP42UL12
Free Airflow @ 50/60 Hz (CFM)*	55	45/55	45/55
Free Airflow @ 50/60 Hz (m <sup>3</sup> /hr.)*	93	76/93	76/93
UNIT CONSTRUCTION			
Noise SIL @ 50/60 Hz (dBA)	65	37/41	37/41
Maximum Operating Temperature (°F/°C)	158/70		
Unit Dimensions - H x W x D (in./mm)	6.29 x 7.37 x 2.65/160 x 187 x 67		
Cutout Dimensions - H x W (in./mm)	5.66 x 5.66/144 x 144		
Weight (lb./kg)	4.2/1.90	4.2/1.90	4.3/1.95
EXHAUST GRILLE CATALOG NUMBERS			
Composite Type 1			
Catalog Number	TEP4		
Stainless Steel Type 1			
Catalog Number	TEP4SS		
Composite Type 12			
Catalog Number	TEP4UL12		

\*CFM with single exhaust grille installed.




**BACK VIEW** 






.45 [12] 1.39

[35]



Exhaust grille included with fan package



CUTOUT DIMENSIONS


89084706




### Performance Data TFP6 Models


ELECTRICAL DATA			
Rated Voltage	24 VDC	115 VAC	230 VAC
Frequency (Hz)	50/60		
Nominal Current Maximum @ 50/60 Hz(Amps)	.88	.45/.36	.23/.18
Power Consumption Maximum @ 50/60 Hz (Watts)	21.1	36/32	39/35
Power Connection	Stripped Leadwires		
CATALOG NUMBERS			
Composite Type 1			
Catalog Number	TFP624	TFP61	TFP62
Stainless Steel Type 1			
Catalog Number	—	TFP61SS	TFP62SS
Composite Type 12			
Catalog Number		TFP61UL12	TFP62UL12
Free Airflow @ 50/60 Hz (CFM)*	140	117/140	117/140
Free Airflow @ 50/60 Hz (m³/hr.)*	238	199/238	199/238
UNIT CONSTRUCTION			
Noise SIL @ 50/60 Hz (dBA)	62.5	50/56	50/56
Maximum Operating Temperature (°F/°C)		158/70	
Unit Dimensions - H x W x D (in./mm)	7.80 x 8.87 x 3.75/198 x 225 x 95		
Cutout Dimensions - H x W (in./mm)	7.16 x 7.16/182 x 182		
Weight (lb./kg)	5.3/2.40	5.3/2.40	5.4/2.45
EXHAUST GRILLE CATALOG NUMBERS			
Composite Type 1			
Catalog Number	TEP6		
Stainless Steel Type 1			
Catalog Number	TEP6SS		
Composite Type 12			
Catalog Number	TEP6UL12		

\*CFM with single exhaust grille installed.






SIDE VIEW



CUTOUT DIMENSIONS

**BACK VIEW** 



Exhaust grille included with fan package

89084710



2.14


6.88 [175]

> 11.16 [283]

## Performance Data TFP10 Models


ELECTRICAL DATA				
Rated Voltage	115 VAC	230 VAC		
Frequency (Hz)	50	50/60		
Nominal Current Maximum @ 50/60 Hz(Amps)	.58/.70	.29/.35		
Power Consumption Maximum @ 50/60 Hz (Watts)	64/80	64/80		
Power Connection	Stripped I	Stripped Leadwires		
CATALOG NUMBERS				
Composite Type 1				
Catalog Number	TFP101	TFP102		
Stainless Steel Type 1				
Catalog Number	TFP101SS	TFP102SS		
Composite Type 12				
Catalog Number	TFP101UL12	TFP102UL12		
Free Airflow @ 50/60 Hz (CFM)*	180/215	180/215		
Free Airflow @ 50/60 Hz (m <sup>3</sup> /hr.)*	306/365	306/365		
UNIT CONSTRUCTION				
Noise SIL @ 50/60 Hz (dBA)	54/61	54/61		
Maximum Operating Temperature (°F/°C)	167/75	167/75		
Unit Dimensions - H x W x D (in./mm)		25/300 x 330 x 133		
Cutout Dimensions - H x W (in./mm)		6/283 x 283		
Weight (lb./kg)	12.0/5.44	11.4/5.17		
EXHAUST GRILLE CATALOG NUMBERS				
Composite Type 1				
Catalog Number	TEP10			
Stainless Steel Type 1				
Catalog Number	TEP	TEP10SS		
Composite Type 12				
Catalog Number	TEP1	TEP10UL12		
*CFM with single exhaust grille installed.				

\*CFM with single exhaust grille installed.






# **TEP10 EXHAUST GRILLE**



Exhaust grille included with fan package





-

1.32 [34]

.55 [14]

# FAN GRILLE

11.89 [302]

11.16 [283]

.37 [9]

## CUTOUT DIMENSIONS






## **TFP EXHAUST GRILLES**



CATALOG NUMBERS	Nominal Fan Size
TEP4 Models	
TEP4	4
TEP4SS	4
TEP4UL12	4
TEP6 Models	
TEP6	6
TEP6SS	6
TEP6UL12	6
TEP10 Models	
TEP10	10
TEP10SS	10
TEP10UL12	10

#### **TFP OPTIONAL GRILLES AND REPLACEMENT FILTERS**



Optional grilles offer the choice of stainless steel or black ABS plastic. These grilles replace the standard RAL 7035 gray composite or stainless steel grilles on both fan and exhaust packages. Standard replacement filters are washable foam [Type 1] or disposable (Type 12). To maintain UL Type 12 rating on the enclosure, UL Type 12 filters must be used on the fan package inlet. Washable aluminum filters are also available. Aluminum filters are compatible with Type 1 systems only. *Type 12 air filters are not washable.* 

CATALOG NUMBERS	Description	Fits Fan and Exhaust Nominal Size	Fits Fan and Exhaust Grill Size (in./mm)
4-inch Fan Models			
TG4SS	Brushed stainless steel grille	4	6.29 x 7.31 x .81 160 x 186 x 21
TG4B	Black ABS plastic grille	4	6.29 x 7.37 x .81 160 x 187 x 21
AFLTR4	Type 1 filter replacement (5/package)	4	_
AFLTR4AL	Aluminum filter replacement (5/package)	4	_
TFLT4UL12	Type 12 filter replacement (5/package)	4	_
6-inch Fan Models			
TG6SS	Brushed stainless steel grille	6	7.80 x 8.81 x .75 198 x 224 x 19
TG6B	Black ABS plastic grille	6	7.80 x 8.87 x .49 198 x 225 x 12
AFLTR6	Foam filter replacement (5/package)	6	_
AFLTR6AL	Aluminum filter replacement (5/package)	6	_
TFLT6UL12	UL 12 filter replacement (5/package)	6	_
10-inch Fan Models			
TG10SS	Brushed stainless steel grille	10	11.81 x 12.92 x .75 300 x 328 x 19
TG10B	Black ABS plastic grille	10	11.81 x 12.99 x .75 300 x 330 x 19
AFLTR10	Foam filter replacement (5/package)	10	_
AFLTR10AL	Aluminum filter replacement (5/package)	10	_
TFLT10UL12	UL 12 filter replacement (5/package)a	10	_

Replacement filter for Type 12 fan package only (models TFF\_UL12). For Type 12 exhaust package use replacement filter AFLTRX. Filters fit all fan and exhaust packages according to their size.

Hoffman

# **TFP EMC UPGRADE KIT**

With the addition of this kit, the cooling fan and exhaust packages are upgraded to provide EMC (electromagnetic compatibility) protection. Consult Hoffman for shielding effectiveness (dB attenuation vs. frequency). Separate kits must be installed on both the inlet and outlet. Cooling fan and exhaust package must be ordered separately. EMC upgrade kit will not work with stainless steel grille option.

CATALOG NUMBERS	Fits Cooling Fan Package	Fits Exhaust Grille
4-inch Fan Models		
T4EMC	TFP41/TFP42	TEP4
6-inch Fan Models		
T6EMC	TFP61/TFP62	TEP6
10-inch Fan Models		
T10EMC	TFP101/TFP102	TEP10

