



Technical Characteristics

Roller Material	Stainless Steel
Actuator	Roller
Actuation	Horizontal - Parallel
Actuator Action	Momentary
Roller Dimension	0.5 Inch (13mm)
Operating Torque/Force	80 Ounces
Application	Machine tools, earth moving equipment or general transportation
Approvals	UL Listed - CSA Certified - CE Marked
Contact Configuration	1 NO/1 NC
Body Material	Cast Zinc (fully potted)
Cable Length	9 Feet
Connection Type	#18 AWG SJTO Cable (Yellow)
Contact Form	Form C (SPDT)
Contact Operation	Snap Action
Contact Material	Silver Alloy
Operating Temperature Range	-4°F to 221°F (-20°C to 105°C)
Degree of Protection	IP 67
Ampere Rating	10A
Head Type	Top Plunger
Type	MS
Shock Resistance	35G
Maximum Voltage Rating	240Vac/28Vdc
Mounting Type	Shoulder
Vibration Resistance	10G (75 to 1200Hz)
Enclosure Rating	NEMA 1/2/4/6/6P/12/13

Shipping and Ordering

Category	22431 - Limit Switches, Miniature, Difficult Applications, Type MS
Discount Schedule	T
GTIN	00785901550587
Package Quantity	1
Weight	1.04 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

document.

Generated: 08/11/2011 10:30:20