


KEMET Part Number: C340C224K2R5TA
(C340C224K2R5TABULK)

Capacitor, ceramic, 0.22 uF, +/-10% Tol, 200 V, X7R, Lead Spacing=0.2"



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.36	MAX
H	8.13	MAX
T	4.07	MAX
S	5.08	NOM
LL	7	MIN
F	0.51	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

General Information	
Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	X7R
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	0.22 uF
Voltage:	200 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	2.5%
Insulation Resistance:	4.55 GOhm
Dielectric Strength:	500 V