


Capacitor, ceramic, 4700 pF, +/-20% Tol, 400 V, Y5U, Lead Spacing=10 mm

**Dimensions (mm)**

Symbol	Dimension	Tolerance
D	14	MAX
T	5	MAX
S	10	+/-1
LL	18	+2/-0
F	0.5	+/-0.1

Packaging Specifications

Package Kind:	Ammo
Package Quantity:	1000

General Information

Supplier:	KEMET
Application:	Safety:X1/Y1
Temperature Coefficient:	Y5U
Body Type:	Radial Disc
Lead Form:	vcrimp
Termination Type:	Tin (Sn)
RoHS:	Yes
Halogen Free:	Yes

Specifications

Capacitance:	4700 pF
Voltage:	400 VAC (X)
Voltage:	250 VAC (Y)
Tolerance:	+/-20%
Temperature Range:	-25/+125C
Failure Rate:	N/A
Dissipation Factor:	2.5%
Insulation Resistance:	10 GOhm
Dielectric Strength:	4000 V