

Fits Printer Models	Diagram	Catalog #	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
<b>Stronger adhesive for textured surfaces (B-422 gloss white):</b>										
TLS, BMP71*	Fig. 34	PTL-39-422	B-422	Polyester	White	0.375 (9.5)	0.600 (15.2)	1	750	R6010
TLS, BMP71*	Fig. 33	PTL-46-422	B-422	Polyester	White	0.375 (9.5)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-5-422	B-422	Polyester	White	0.500 (12.7)	0.200 (5.1)	1	750	R6010
TLS, BMP71*	Fig. 29	PTL-44-422	B-422	Polyester	White	0.500 (12.7)	0.375 (9.5)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-7-422	B-422	Polyester	White	0.500 (12.7)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 33	PTL-8-422	B-422	Polyester	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-16-422	B-422	Polyester	White	1.000 (25.4)	0.375 (9.5)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-17-422	B-422	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 40	PTPSL-17-422	B-422	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-19-422	B-422	Polyester	White	1.000 (25.4)	1.000 (25.4)	1	250	R6010
TLS, BMP71*	Fig. 29	BM71-20-422	B-422	Polyester	White	1.000 (25.4)	2.000 (50.8)	1	1000	R6010
TLS, BMP71*	Fig. 33	PTL-42-422	B-422	Polyester	White	1.000 (25.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-45-422	B-422	Polyester	White	1.050 (38.1)	0.375 (9.5)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-29-422	B-422	Polyester	White	1.050 (38.1)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-30-422	B-422	Polyester	White	1.500 (38.1)	0.750 (19.1)	1	250	R6010
TLS, BMP71*	Fig. 29	PTL-32-422	B-422	Polyester	White	1.500 (38.1)	1.500 (38.1)	1	250	R6010
TLS, BMP71*	Fig. 33	PTL-43-422	B-422	Polyester	White	1.900 (48.3)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-20-422	B-422	Polyester	White	2.000 (50.8)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 40	PTPSL-20-422	B-422	Polyester	White	2.000 (50.8)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 40	PTPSL-26-422	B-422	Polyester	White	2.750 (69.9)	1.250 (31.8)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-22-422	B-422	Polyester	White	3.000 (76.2)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 40	PTPSL-50-422	B-422	Polyester	White	3.000 (76.2)	1.650 (41.9)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-37-422	B-422	Polyester	White	3.000 (76.2)	1.900 (48.3)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-23-422	B-422	Polyester	White	4.000 (101.6)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-38-422	B-422	Polyester	White	4.000 (101.6)	1.900 (48.3)	1	100	R6010
TLS, BMP71*	Fig. 54	PTL-35-422-PPROP	B-422	Polyester	Gray	1.630 (41.4)	0.750 (19.1)	1	250	R6010
<b>Stronger adhesive for textured surfaces (B-432 clear):</b>										
TLS, BMP71*	Fig. 33	PTL-8-432	B-432	Polyester	Clear	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-10-432	B-432	Polyester	Clear	0.750 (19.1)	0.250 (6.4)	1	750	R6010
TLS, BMP71*	Fig. 29	PTL-11-432	B-432	Polyester	Clear	0.750 (19.1)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-17-432	B-432	Polyester	Clear	1.000 (25.4)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 33	PTL-42-432	B-432	Polyester	Clear	1.000 (25.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 33	PTL-43-432	B-432	Polyester	Clear	1.900 (48.3)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
<b>Ultra aggressive adhesive for highly textured surfaces (B-483 gloss white):</b>										
TLS, BMP71*	Fig. 33	PTL-101-483	B-483	Polyester	White	0.250 (6.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 33	PTL-8-483	B-483	Polyester	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-16-483	B-483	Polyester	White	1.000 (25.4)	0.375 (9.5)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-17-483	B-483	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-19-483	B-483	Polyester	White	1.000 (25.4)	1.000 (25.4)	1	250	R6010
TLS, BMP71*	Fig. 33	PTL-42-483	B-483	Polyester	White	1.000 (25.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 46	PTL-24-483-BK	B-483	Polyester	White	1.130 (28.7)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 33	PTL-100-483	B-483	Polyester	White	1.300 (33.0)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 29	PTL-65-483	B-483	Polyester	White	1.375 (34.9)	1.000 (25.4)	1	250	R6010
TLS, BMP71*	Fig. 29	PTL-29-483	B-483	Polyester	White	1.500 (38.1)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-30-483	B-483	Polyester	White	1.500 (38.1)	0.750 (19.1)	1	250	R6010
TLS, BMP71*	Fig. 29	PTL-31-483	B-483	Polyester	White	1.500 (38.1)	1.000 (25.4)	1	250	R6010
TLS, BMP71*	Fig. 29	PTL-32-483	B-483	Polyester	White	1.500 (38.1)	1.500 (38.1)	1	250	R6010
TLS, BMP71*	Fig. 33	PTL-43-483	B-483	Polyester	White	1.900 (48.3)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 28	PTL-61-483	B-483	Polyester	White	2.000 (50.8)	0.500 (12.7)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-20-483	B-483	Polyester	White	2.000 (50.8)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-37-483	B-483	Polyester	White	3.000 (76.2)	1.900 (48.3)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-62-483	B-483	Polyester	White	4.000 (101.6)	0.750 (19.1)	1	50	R6010
TLS, BMP71*	Fig. 29	PTL-23-483	B-483	Polyester	White	4.000 (101.6)	1.000 (25.4)	1	100	R6010
TLS, BMP71*	Fig. 29	PTL-63-483	B-483	Polyester	White	8.000 (101.6)	0.750 (19.1)	1	50	R6010
<b>Ultra aggressive adhesive for highly textured surfaces (B-489 matte white):</b>										
TLS, BMP71*	Fig. 33	PTL-101-489	B-489	Polyester	White	0.250 (6.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R4310
TLS, BMP71*	Fig. 33	PTL-8-489	B-489	Polyester	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R4310
TLS, BMP71*	Fig. 29	PTL-16-489	B-489	Polyester	White	1.000 (25.4)	0.375 (9.5)	1	500	R4310
TLS, BMP71*	Fig. 29	PTL-17-489	B-489	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R4310
TLS, BMP71*	Fig. 29	PTL-19-489	B-489	Polyester	White	1.000 (25.4)	1.000 (25.4)	1	250	R4310
TLS, BMP71*	Fig. 33	PTL-42-489	B-489	Polyester	White	1.000 (25.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R4310
TLS, BMP71*	Fig. 33	PTL-100-489	B-489	Polyester	White	1.300 (33.0)	50 ft. (15.2 m)	1	1 Roll Cont.	R4310
TLS, BMP71*	Fig. 29	PTL-29-489	B-489	Polyester	White	1.500 (38.1)	0.500 (12.7)	1	500	R4310
TLS, BMP71*	Fig. 29	PTL-30-489	B-489	Polyester	White	1.500 (38.1)	0.750 (19.1)	1	250	R4310
TLS, BMP71*	Fig. 29	PTL-31-489	B-489	Polyester	White	1.500 (38.1)	1.000 (25.4)	1	250	R4310
TLS, BMP71*	Fig. 29	PTL-32-489	B-489	Polyester	White	1.500 (38.1)	1.500 (38.1)	1	250	R4310
TLS, BMP71*	Fig. 33	PTL-43-489	B-489	Polyester	White	1.900 (48.3)	50 ft. (15.2 m)	1	1 Roll Cont.	R4310
TLS, BMP71*	Fig. 29	PTL-20-489	B-489	Polyester	White	2.000 (50.8)	1.000 (25.4)	1	100	R4310
TLS, BMP71*	Fig. 29	PTL-37-489	B-489	Polyester	White	3.000 (76.2)	1.900 (48.3)	1	100	R4310
TLS, BMP71*	Fig. 29	PTL-38-489	B-489	Polyester	White	4.000 (101.6)	1.900 (48.3)	1	100	R4310
<b>Chemical resistant (B-488 matte white):</b>										
TLS, BMP71*	Fig. 29	PTL-80-488	B-488	Polyester	White	0.750 (19.1)	0.900 (22.9)	1	250	R4310
TLS, BMP71*	Fig. 29	PTL-97-488	B-488	Polyester	White	0.900 (22.9)	0.900 (22.9)	1	250	R4310
TLS, BMP71*	Fig. 29	PTL-81-488	B-488	Polyester	White	1.900 (48.3)	0.250 (6.3)	1	750	R4310
TLS, BMP71*	Fig. 29	PTL-78-488	B-488	Polyester	White	1.900 (48.3)	1.000 (25.4)	1	250	R4310

See all TLS2200® and PC Link™ Ribbon parts on page 323.

\* Yellow media adaptor required for use in the BMP®71 printer. See page 324.

