

Harsh Environment Connectivity Solutions



Rear (0.250 mounting hole) and Front (0.469 mounting hole) Pushbutton Switches

These small momentary switches are completely enclosed in rugged metal housing. Front or rear-panel mount types offer 1-A, 1-B, 1-C, or 1-D switching. Red or black pushbuttons and solder terminals are standard.

SPECIFICATIONS

Body: Copper alloy, plated.

Pushbutton: Molded red or black plastic, integral with shaft.

Insulation: Rigid plastic.

Springs: Integral contacts, plated.

Ratings: 250 mA, 30 W maximum, AC, non-inductive load.

Solder Terminals: Copper alloy, silver-plated.

Locknuts: Copper alloy, plated.

Series 903, 913: P-1053-1.

Series 923, 933: P-1150-1.

Lockwasher: Series 903, 913: Steel, P-1060-3

Flat Washer: Series 923, 933: Steel, plated,

S-1790-1

SPECIAL ORDER FEATURES

* Other pushbutton colors.

* Legends.

PART NUMBERS

Panel Mounting	Pushbutton Color/ Part Number		Circuit
	Red	Black	
Front	903	913	1-C
	*903D	*913D	1-D
Rear	923	933	1-C
	*923D	933D	1-D

^{*} Special order only; contact Switchcraft for price and delivery.