

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731710700](#)
Status: **Active**
Overview: [BNC RF Connectors](#)
Description: 75 Ohms, BNC Right-Angle, Low Profile, PCB Jack Receptacle

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	RF/Coax Connectors
Series	73171
Overview	BNC RF Connectors
Product Name	BNC
Style	PCB
UPC	800754027007
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	11.524/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead
Reverse Polar	No
Electrical	
Impedance	75#
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73171-070



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Contained Per -ED/79/2015 (17 December 2015) Halogen-Free Status Not Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV
	50 Image Not Relevant

Search Parts in this Series
[73171](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION