



Datasheet for part number D38999/26FA98SA

Our Catalog Part Number: D3899926FA98SA
Our Global Manufacturing Part Number: 113009-0750
Brand: Cannon Product Category: Circular Product Line: 38999 Series I, II, and III Series: KJ

Product Datasheet	
SERIES	MIL - DTL - 38999 Series III
STYLE	Straight plug
CLASS	Environment resistant (without rear accessory)
SHELL SIZE	9
SHELL MATERIAL	Corrosion resistant shells of aluminum alloy
INSULATOR MATERIAL	High grade plastic
GROMMET AND SEAL MATERIAL	Silicone base elastomer
PLATING	Electroless nickel
ARRANGEMENT	9-98
NUMBER OF CONTACTS	3 contacts size 20
GENDER	Socket
CONTACT TYPE	Rear release crimp snap-in contacts
CONTACT MATERIAL	Copper Alloy, gold plate
POLARIZATION	AR° or AP° BSC=102° BR° or BP° BSC=132° CR° or CP° BSC=248°
LOW PROFILE / LIGHT WEIGHT	no
SCOOP PROOF	yes
COUPLING SYSTEM	Threaded coupling
ELECTROLYTIC EROSION	yes
DURABILITY (CYCLES)	500
HIGH IMPACT SHOCK	yes
EXTERNAL BENDING MOMENT (Size 25)	1000 in/lbs
RANDOM VIBRATION "J"	492 F
SINE VIBRATION	60 G, 85 to +392 F
SAND, DUST, ICE	yes
TEMPERATURE RANGE	65°C (85°F) to + 200°C (+392°F)
CORROSION RESISTANT	48 hours
TEST SERVICE RATING (MATED)	Sea Level = 1800 50000 ft. = 1000 70000 ft. = 1000 100000 ft. = 1000
TEST SERVICE RATING (UNMATED)	Sea Level = 1800 50000 ft. = 600 70000 ft. = 400 100000 ft. = 200
OPERATING VOLTAGE	Vrms = 600 Vdc = 850