

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193240001](#)
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp™ Metric Ring Terminal for Stud Size 4 (M2.6), Insulated Barrel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19324](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Metric Ring Terminals](#)
 Product Name Avikrimp™
 Type Ring
 UPC 887191290010

Physical

Barrel Type Closed - Brazed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 0.781/g
 Packaging Type Bag
 Stud Size M2.5
 Wire Size AWG N/A
 Wire Size mm² 0.50-1.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number AA1-832-M2,5

Reference - Drawing Numbers

Sales Drawing SD-19324-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[19324 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100