

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0193240009](#)  
**Status:** **Active**  
**Overview:** Metric Ring Terminals  
**Description:** Avikrimp™ Metric Ring Terminal for Stud Size 5 (M3), Insulated Barrel

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19324](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Metric Ring Terminals](#)  
 Product Name Avikrimp™  
 Type Ring  
 UPC 887191290096

**Physical**

Barrel Type Closed - Brazed  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper Alloy  
 Material - Plating Mating Tin  
 Net Weight 1.068/g  
 Packaging Type Bag  
 Stud Size M5  
 Wire Size AWG N/A

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Old Part Number BB2,5-839-M5

**Reference - Drawing Numbers**

Sales Drawing SD-19324-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

**Search Parts in this Series**

[19324](#) Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
PremiumGrade™	<a href="#">0640010100</a>
Hand Crimp Tool	
Crimp Head for the	<a href="#">0640050100</a>
AT-200™ Pneumatic	
Hand Tool	