

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240014

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp™ Metric Ring Terminal for Stud Size 1/4" (M6), Insulated Barrel

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19324

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Metric Ring Terminals

Product Name

Avikrimp™

Type

Ring

UPC

887191290140

Physical

Barrel Type

Closed - Brazed

Flammability

94V-2

Insulation

Nylon (PA)

Material - Metal

Copper Alloy

Material - Plating Mating

Tin

Net Weight

2.828/g

Packaging Type

Bag

Stud Size

M8

Wire Size AWG

N/A

Wire Size mm²

2.50-6.00

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Old Part Number

C6-830-M6

Reference - Drawing Numbers

Sales Drawing

SD-19324-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

19324 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION