ATTENUATORS



QC10 CLASSIC

SINGLE-GANG

UL LISTED, 20W, 10-Step,
Stainless Steel Faceplate, Printed Positions

GENERAL DESCRIPTION

The **QC10 CLASSIC** is a UL Listed, single-gang, 20W, ten-step, continuous rotary, audio level attenuator with an OFF position. Brushed, stainless steel faceplate with printed positions and a black knob with white indicator mark.

INTENDED USE - Indoor Environment

Primary Use Attenuates audio power to any number of loudspeakers, up to 20W load. For use with 25V or 70V distributed audio systems.

UL LISTED 813 When installed in accordance with supplied instructions and connected to supply circuits in accordance with ANSI/NFPA70, NEC, and AHJ.

Installation | Single-gang electrical box, 2-1/8"D

AUDIO SPECIFICATIONS

Power Rating
Attenuation
(Ref: 25V, 70.7V line)

Ref: 25V, 70.7V line)

Insertion Loss
Audio Connection


Autenuation
Position 10 : Full Signal
Position 9-3 : -3 dB each
Positions 2-1 : -6 dB each
Position 0 : No Signal

40.5 dB
10" long, pre-cut, color coded leads

RECOMMENDED QUAM COMPONENTS

Enclosures | Surface Mount : SE4W





Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at: www.QuamSpeakers.com









QUAM-NICHOLS COMPANY, INC. 234 East Marquette Rd. Chicago, IL. 60637 Tel: 1-800-NEED-NOW (800-633-3669) Fax: 1-888-NEED-NOW (888-633-3669) e-mail: NeedNow@QNC.com www.QuamSpeakers.com