Revision Number: 006.1

Issue date: 06/27/2016

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: **LOCTITE® 243™ THREADLOCKER**
Product type: Anaerobic
Restriction of Use: None identified
Company address:
Henkel Corporation
One Henkel Way
Rocky Hill, Connecticut 06067

IDH number: 1329837
Item number: 1329837
Region: United States
Contact information:
Telephone: (860) 571-5100
MEDICAL EMERGENCY Phone: Poison Control Center
1-877-671-4608 (toll free) or 1-303-592-1711
TRANSPORT EMERGENCY Phone: CHEMTREC
1-800-424-9300 (toll free) or 1-703-527-3887
Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW	
WARNING:	CAUSES SKIN IRRITATION. MAY CAUSE AN ALLERGIC SKIN REACTION. CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)

Precautionary Statements

Prevention: Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.

Response: IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

Storage: Not prescribed

Disposal: Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*

Polyglycol dimethacrylate	Proprietary	10 - 30
Methacrylate resin	Proprietary	10 - 30
Propane-1,2-diol	57-55-6	1 - 5
Cumene hydroperoxide	80-15-9	0.1 - 1
1-Acetyl-2-phenylhydrazine	114-83-0	0.1 - 1
Cumene	98-82-8	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.

Skin contact: Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). Wash clothing before reuse. Get medical attention.

Eye contact: Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Ingestion: DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.

Symptoms: See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media: Water spray (fog), foam, dry chemical or carbon dioxide.

Special firefighting procedures: Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.

Unusual fire or explosion hazards: Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.

Hazardous combustion products: Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic fragments.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions: Do not allow product to enter sewer or waterways.

Clean-up methods: Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling: Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Use only with adequate ventilation. Refer to Section 8.

Storage: For safe storage, store at or below 38 °C (100.4 °F)
Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyglycol dimethacrylate	None	None	None	None
Methacrylate resin	None	None	None	None
Propane-1,2-diol	None	None	10 mg/m3 TWA Aerosol.	None
Cumene hydroperoxide	None	None	1 ppm (6 mg/m3) TWA (SKIN)	None
1-Acetyl-2-phenylhydrazine	None	None	None	None
Cumene	50 ppm TWA	50 ppm (245 mg/m3) PEL (SKIN)	None	None

Engineering controls: Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection: Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection: Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection: Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Butyl rubber gloves. Neoprene gloves. Natural rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Liquid
Color: Blue
Odor: Characteristic
Odor threshold: Not available.
pH: Not available.
Vapor pressure: < 0.1 mm hg (27 °C (80.6 °F))
Boiling point/range: > 149 °C (> 300.2 °F)
Melting point/ range: Not available.
Specific gravity: 1.09
Vapor density: Not available.
Flash point: > 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower: Not available.
Flammable/Explosive limits - upper: Not available.
Autoignition temperature: Not available.
Flammability: Not applicable
Evaporation rate: Not available.
Solubility in water: Slight
Partition coefficient (n-octanol/water): Not available.
VOC content: 1.09 %; 11.88 g/l
Viscosity: Not available.

Decomposition temperature: Not available.

10. STABILITY AND REACTIVITY

Stability: Stable under normal conditions of storage and use.

Hazardous reactions: None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials.

Hazardous decomposition products: Oxides of carbon. Oxides of nitrogen. Oxides of sulfur. Irritating organic fragments.

Incompatible materials: Strong oxidizing agents. Reducing agents. Strong alkalis. Oxygen scavengers. Other polymerization initiators. Heavy metals.

Reactivity: Not available.

Conditions to avoid: Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact: Causes skin irritation. May cause allergic skin reaction.
Eye contact: Causes serious eye irritation.
Ingestion: May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Polyglycol dimethacrylate	None	Allergen, Irritant
Methacrylate resin	None	Irritant, Allergen
Propane-1,2-diol	Oral LD50 (Rabbit) = 18 g/kg Oral LD50 (Mouse) = 23.9 g/kg Oral LD50 (Rat) = 30 g/kg	Irritant
Cumene hydroperoxide	Inhalation LC50 (Mouse, 4 h) = 200 mg/l	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
1-Acetyl-2-phenylhydrazine	Oral LD50 (Mouse) = 270 mg/kg	Allergen, Blood, Kidney, Mutagen, Some evidence of carcinogenicity
Cumene	Oral LD50 (Rat) = 2.91 g/kg Oral LD50 (Rat) = 1,400 mg/kg Inhalation LC50 (Rat, 4 h) = 8000 ppm	Central nervous system, Irritant, Lung

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyglycol dimethacrylate	No	No	No
Methacrylate resin	No	No	No
Propane-1,2-diol	No	No	No
Cumene hydroperoxide	No	No	No
1-Acetyl-2-phenylhydrazine	No	No	No
Cumene	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: RQ, Environmentally hazardous substance, liquid, n.o.s.
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
DOT Hazardous Substance(s): alpha,alpha-Dimethylbenzylhydroperoxide

International Air Transportation (ICAO/IATA)

Proper shipping name: RQ, Environmentally hazardous substance, liquid, n.o.s. (Fatty acid amide)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: RQ, ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Fatty acid amide)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: Fatty acid amide

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis.
CERCLA Reportable quantity: Cumene hydroperoxide (CAS# 80-15-9) 10 lbs. (4.54 kg)

California Proposition 65: This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: Reviewed SDS. Reissued with new date.

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 06/27/2016

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.