





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED TO PRODUCTION	4/13/00	R. CARRICK
B	ADDED GROUND TAB. SEE ECN # 1030	11/15/01	R. CARRICK
C	PRODUCT VALIDATION UPDATES (ECN 1204)	01/14/03	MCCORMICK
D	ECN# 2731 - ADDED ROHS STAMP	10/23/07	D.GRIFFIN



2X MINI DIN 4 FEMALE




RECOMMENDED PANEL OPENING

NOTES:

1. D-FLAT AND RECTANGULAR SLOT ARE PARALLEL TO EACH OTHER.
2. PINS ARE WIRED STRAIGHT THROUGH.
3. FINISH: NICKEL PLATED BRIGHT.
4. INTERNAL TOOTH LOCK WASHER AND HEX NUT INCLUDED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 TOLERANCES TO BE:
 .X ±.1 [2.5] ANGLES ±2°
 .XX ±.01 [.25]
 .XXX ±.005 [.13]
 OVERALL CABLE LENGTH TOL:
 ≤ 60 [1524] +3 [76.2] / -0
 > 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY RON CARRICK	4/13/2000
CHECKED BY DFP	4/13/2000
APPROVED BY T.J.C.	4/13/2000

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		AUDIO VIDEO	
PRODUCT DESCRIPTION		MIN DIN-4 ADAPTOR	
SIZE A	FSCM NO. 43321	DWG. NO. MD44FF	REV. D
SCALE: NONE		CAD FILE: MD44FF.SLDDRW	
		SHEET 1 OF 1	