

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192050012

Status:

Active

Overview:

Splices

Description:

VersaKrimp™ Butt Splice for 3/0 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

UPC

Splices

19205

Yes

N/A

Splices

Butt, VersaKrimp™

800755060935

Physical

Barrel Type

Insulation

Material - Metal

Material - Plating Mating

Material - Plating Termination

Packaging Type

Wire Size AWG

Closed - Brazed

None

Copper

Tin

Tin

Bag

3/0

Material Info

Old Part Number

K-393


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011, PS-19902-013

SD-19215-007



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

19205 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Die Set (large) for the HHLS Hydraulic Crimper	0192900028
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION