

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200840030](#)
Status: **Active**
Overview: Brad® Ultra-Lock® Connection System
Description: Ultra-Lock® (M12) Ethernet Receptacle, Female (Straight), , 5 Poles, 5.00mm stand-off

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120084
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	Brad® Ultra-Lock® Connection System
Product Name	Ultra-Lock® (M12)
Type	PCB Mount
UPC	78678812018

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Orientation	Straight
Panel Mount	Back
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Old Part Number	WR5U40000
-----------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-120084-009
---------------	---------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[120084 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION