




FEATURES:

- Cable is ideal in audio applications where a low impedance shielded balance line is desired.
- The two conductors in the cable are manufactured by an Electrolytic Tough Pitch process to ensure high copper purity. High copper purity provides superb electrical conductivity.
- Banana plugs feature Beryllium Copper springs for long insertion life & can be stacked horizontally/vertically.
- Banana plugs are molded directly to the cable and wires for robust pull strength.

MATERIALS:

Banana Plugs (Single and Double):

Body: Brass, Nickel Plated

Spring: Beryllium Copper, Nickel Plated

Insulation: Polypropylene, Color: Double – Gray, Single – Green

Two Conductors, Shielded Microphone Type Cable:

Two Conductors: 22 AWG, Standing 16 x 34 t.c.

Shield: Tinned Copper, Braided

Jacket: PVC, O.D. .231" (5,87mm) Nom., Color: Gray, Marking: " POMONA 1167-*.

Shield Leads: 20 AWG, Stranding 41 x 36 t.c., PVC Insulated .087" (2,21mm) O.D., Color: Green

RATING:

Operating Voltage: 1000 VRMS

Operating Temperature: +55°C (+131°F)

ORDERING INFORMATION: Model 1167-XX

XX = Cable Length in Inches. Standard Lengths: 18" (45,72cm), 24" (60,96cm), 30" (76,20cm), 36" (91,44cm), 48" (121,92cm), 60" (152,40cm).

Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA