

LED Panel Series



VT-605 RD

HIGHLIGHTS :

WATTS



6

EQ. WATTS



35

LUMINOUS



420

BEAM ANGLE



120

Item No	: VT-605 RD
SKU Code	: 4904
Watts	: 6
EQ Watts	: 35
Voltage	: 85-265V,50/60Hz
Lumen(lm)	: 420
Color Temperature	: 3000K
Beam Angle	: 120
Commercial type	: ROUND
PF	: >0.9
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20
Body type	: ALUMINUM
Dimmable	: Yes
Operation Temperature	: -20~50°C
EAN code	: 3800157605380
Unit size	: D:90x24mm
Packing details	: 40
Unit cbm	: 0.000311

PRODUCT FEATURES

- Compare with incandescent, it can save over 80% electric cost
- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiaiton
- No Lead or Mercury content hence Environment friendly
- Suitable for office and genral lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45°C

[CLICK HERE FOR OTHER RELATED CERTIFICATES](#) 