

LED Floodlights



VT-4822

HIGHLIGHTS :

WATTS



20

EQ. WATTS



80

LUMINOUS



1600

BEAM ANGLE



120

Item No	: VT-4822
SKU Code	: 5692
Watts	: 20
EQ Watts	: 80
Voltage	: 85-265V,50/60Hz
Lumen(lm)	: 1600
Color Temperature	: 4000K
Beam Angle	: 120
PF	: >0.95
LED Chip Type	: SMD
CRI	: >70
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP54
Body type	: DIE CAST ALUMINUM
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157603515
Unit size	: 208x204x355mm
Packing details	: 10
Unit cbm	: 0.0056

PRODUCT FEATURES

- Available in White , Warm White and RGB Light output option
- Premium Quality Aluminium Alloy body
- Corrosion Resistant
- Built in Power supply, No external ballast required
- PIR Sensor Movement Detector – Optional
- Widely used for Lighting Driveways, Gardens & Buildings, Commercial Bill,Boards & Hoardings, Plazas,Sports Grounds & Parking Lots

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES 