

LED Spotlights



VT-1849

HIGHLIGHTS :

WATTS



4

EQ. WATTS



30

LUMINOUS



320

BEAM ANGLE



150

Item No	: VT-1849
SKU Code	: 4296
Watts	: 4
EQ Watts	: 30
Base / holder	: G9
Voltage	: 220-240V,50/60Hz
Lumen(lm)	: 320
Color Temperature	: 4000K
Beam Angle	: 150
PF	: >0.4
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230628978
Unit size	: D:23x65mm
Packing details	: 400
Unit cbm	: 7.2E-05

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES 