

LED Spotlights



VT-2889

HIGHLIGHTS :

WATTS



8

EQ. WATTS



80

LUMINOUS



750

BEAM ANGLE



38

Item No	: VT-2889
SKU Code	: 1694
Watts	: 8
EQ Watts	: 80
Base / holder	: GU10
Voltage	: 220-240V,50Hz
Lumen(lm)	: 750
Color Temperature	: 4000K
Beam Angle	: 38
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20
Body type	: PLASTIC
Dimmable	: No
Life Time	: 20,000 HOURS
Operation Temperature	: -20~50'C
EAN code	: 3800157608954
Unit size	: 50mm x 55mm
Packing details	: 200
Unit cbm	: 0.000138

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting

CLICK HERE
FOR OTHER RELATED CERTIFICATES

