



1	Lcd Type	TFT
2	View Angle	75/75/75/75
3	Polarizer Mode	TRANSMISSIVE
4	Screen size	5.0(diagonal)
5	Display format	800X 3RGB X 480
6	Operating Temperature	-20°C~70°C
7	Storage Temperature	-30°C~80°C
8	Active area	108.0(h) X 64.8(v)/mm
9	Pixel configuration	RGB-STRYPE
10	Brightness	250min 300 typ. cd/m ²




Midas Components			
MODEL	MCT050ACA01TW800480LML		
TITLE	LCM DRAWING		
DWG NO.	050403		
SCALE:	1/1	UNIT:	mm
REV:	0	PAGE:	1/2
APPROVE			
CHECK			
DRAW	Ben 04/07/16		

The non-specified tolerance of dimension is ±0.3mm.

SCALE 30/1

Pin	Symbol
1	GND
2	VDD
3	BLE
4	D/C
5	WR
6	RD
7	DB0
8	DB1
9	DB2
10	DB3
11	DB4
12	DB5
13	DB6
14	DB7
15	DB8
16	DB9
17	DB10
18	DB11
19	DB12
20	DB13
21	DB14
22	DB15
23	NC
24	NC
25	CS
26	RST
27	NC
28	NC
29	XL
30	YU
31	XR
32	YD
33	VLED-
34	VLED-
35	VLED+
36	VLED+



The non-specified tolerance of dimension is $\pm 0.3\text{mm}$.

Midas Components

MODEL	MCT050ACCA0TW800480LM1		
TITLE	LCM DRAWING		
DWG NO.	050403		
SCALE:	1/1	UNIT:	mm
REV:	0	PAGE:	2/2
APPROVE			
CHECK			
DRAW	Ben 04/07/16		