

acer



FOUR MODES OF BEING

Switch One 10

- **Four modes**
Four modes for work and play – Notebook, Pad, Tent and Display
- **Snap on, snap off**
A latch-less magnetic hinge design makes switching between modes easy
- **See it better**
Everything will look crisp and clear on a 10.1" HD IPS display



Resolution



2-in-1 Device



Office Mobile



Product views	<ol style="list-style-type: none"> Power button Volume button Microphone Webcam 	<ol style="list-style-type: none"> 10.1" display Keyboard Touchpad Headset/speaker jack 	<ol style="list-style-type: none"> Micro USB port DC-in jack HDMI[®] micro connector with HDCP support 	<ol style="list-style-type: none"> Card reader USB 2.0 port
Operating system¹	Windows 10 Home 32-bit			
CPU and chipset¹	Intel [®] Atom [™] x5-Z8300 processor			
Memory^{1,2,3,4}	DDR3L memory support • 2 GB of onboard DDR3L system memory			
Display⁵	10.1" display with IPS (In-Plane Switching) technology, HD 1280 x 800, high-brightness LED-backlit TFT LCD with integrated multi-touch • 16:10 aspect ratio • Wide viewing angle • Mercury free, environment friendly			
Graphics¹	Intel [®] HD Graphics with 3D graphics hardware acceleration			
Audio	Two built-in stereo speakers Built-in digital microphone			
Storage⁶	microSD [™] card 64 GB / 32 GB eMMC Optional 2 nd HDD 500 GB, 2.5-inch 5400 RPM			
Webcam¹	Rear webcam with 1600 x 1200 resolution and 720p HD audio/video recording Front webcam with 1600 x 1200 resolution and 720p HD audio/video recording			
Wireless and networking^{1,7,8}	WLAN: 802.11b/g/n wireless LAN WPAN: Bluetooth [®] 4.0			
Dimensions and weight⁹	Dimensions • 259 (W) x 180.5 (D) x 9.65 (H) mm (10.2 x 7.11 x 0.38 inches) pad only • 259 (W) x 192.6 (D) x 20.65 (H) mm (10.2 x 7.58 x 0.81 inches) pad and dock • 259 (W) x 192.6 (D) x 24.45 (H) mm (10.2 x 7.58 x 0.96 inches) pad and dock with hard drive		Weight • 0.68 kg (1.5 lbs.) with 2-cell battery pack, pad only • 1.26 kg (2.78 lbs.) with 2-cell battery pack, pad and dock • 1.36 kg (3 lbs.) with 2-cell battery pack, pad and dock with hard drive	
Power adapter and battery¹⁰	Power adapter: 2-pin 15 W AC adapter Battery: 31.2 Wh 8200 mAh 3.8 V 2-cell Li-ion battery pack Battery life up to 10 hours			
Input and control	Keyboard: 83-/84-/87-key, 95% full-size Acer FineTip keyboard with international language support Touchpad: Multi-gesture touchpad, supporting two-finger scroll; pinch; gestures to open Cortana, Action Center, multitasking; application commands Control Keys: Volume up and down keys, Windows key			
Sensors	Accelerometer (G-sensor)			
Windows Desktop apps¹¹	• Acer Care Center • Acer Portal • abFiles • abPhoto • Accessory Store • McAfee [®] Internet Security			
Warranty	One-year International Travelers Warranty (ITW)			
1.	Specifications vary depending on model.	7.	Actual throughput may vary depending on network conditions and environmental factors such as network traffic or overhead, building construction and access point settings.	
2.	Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment.	8.	Subject to availability.	
3.	Memory speed may vary, depending on the CPU, chipset or memory fitted.	9.	Weight may vary depending on product configuration, vendor components, manufacturing variability, and selected options.	
4.	A 64-bit operating system is required to enjoy the ultimate performance of 4 GB or higher memory.	10.	Listed battery life is based on MobileMark 2014 [®] productivity mode testing with wireless on. Details of MobileMark 2014 testing are available at www.bapco.com . Battery life rating is for comparison purposes only. Actual battery life varies by model, configuration, application, power management settings, operating conditions, and features used. A battery's maximum capacity decreases with time and use.	
5.	All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products.	11.	Bundled software may vary depending on hardware configuration, OS and regional availability.	
6.	1 GB is 1 billion bytes, 1 TB is 1000 GB. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.			

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region. As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.

© 2016. All rights reserved.

Microsoft and Windows are registered trademarks of Microsoft Corporation.

Intel, Intel Core, Core Inside, Pentium, and Pentium Inside are trademarks of Intel Corporation in the U.S. and other countries.

About Acer

Established in 1976, Acer is a hardware + software + services company dedicated to the research, design, marketing, sale, and support of innovative products that enhance people's lives. Acer's product offerings include PCs, displays, projectors, servers, tablets, smartphones, and wearables. The company is also developing cloud solutions to bring together the Internet of Things. Acer employs 7,000 people and ranks No. 4 for total PCs globally (IDC 2014). Revenues for 2014 reached US\$10.39 billion. Please visit www.acer.com for more information.