

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008560110

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Terminal, 22-30 AWG, Bag, Gold (Au), Nickel (Ni) Under Plating

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-2759-001 (PDF)

General

Product Family

Crimp Terminals

Series

2759

Application

Signal

Crimp Quality Equipment

Yes

Overview

KK® Interconnect System - Molex

Packaging Alternative

08-56-0109 (Reel)

Product Name

KK® 254

UPC

800753614239

Physical

Gender

Female

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Net Weight

0.064/g

Packaging Type

Bag

Plating min - Mating

0.381µm

Plating min - Termination

0.051µm

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.57mm max.

Wire Size AWG

22, 24, 26, 28, 30

Wire Size mm²

N/A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

2759-(550)L

Reference - Drawing Numbers

Packaging Specification

PK-2759-001

Sales Drawing

SD-2759



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

2759 Series

Use With

2695 , 5051

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0638118200
Extraction Tool	0011030022
Insertion Tool	0638120000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION