

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0530150710](#)  
**Status:** **Active**  
**Overview:** [MicroBlade™ Connection System](#)  
**Description:** 2.00mm Pitch MicroBlade™ Wire-to-Board Header, Right Angle, 7 Circuits

**Documents:**

[3D Model](#) [Product Specification PS-51004-002 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family PCB Headers  
 Series [53015](#)  
 Application Signal, Wire-to-Board  
 Overview [MicroBlade™ Connection System](#)  
 Product Name MicroBlade™  
 UPC 800753566446


**Physical**

Breakaway No  
 Circuits (Loaded) 7  
 Circuits (maximum) 7  
 Durability (mating cycles max) 30  
 First Mate / Last Break No  
 Flammability 94V-0  
 Glow-Wire Compliant No  
 Guide to Mating Part No  
 Keying to Mating Part None  
 Lock to Mating Part Yes  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin Nylon  
 Net Weight 648.000/mg  
 Number of Rows 1  
 Orientation Right Angle  
 PC Tail Length 3.50mm  
 PCB Locator No  
 PCB Retention Yes  
 PCB Thickness - Recommended 1.60mm  
 Packaging Type Bag  
 Pitch - Mating Interface 2.00mm  
 Polarized to PCB No  
 Shrouded Fully  
 Stackable No  
 Surface Mount Compatible (SMC) No  
 Temperature Range - Operating -20°C to +85°C  
 Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 2.0A  
 Voltage - Maximum 125V

**Material Info**



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[53015](#) Series

**Mates With**

[51004](#) Crimp Housing, [50011](#) Crimp  
 Terminal

**Reference - Drawing Numbers**

Product Specification

PS-51004-002, RPS-51004-002, RPS-51004-003,  
RPS-51004-008, RPS-51004-010, RPS-51004-011,  
RPS-51004-014, RPS-51004-015, RPS-51004-016,  
RPS-51004-017, RPS-51004-018, RPS-51004-019,  
RPS-51004-020, RPS-51004-021, RPS-51004-022,  
RPS-51004-023, RPS-51004-024, RPS-51004-025,  
RPS-53014-001  
SD-53015-\*\*10

Sales Drawing

This document was generated on 09/30/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**