## **3M**

## 46 Electrical Tape

Polyester Film/Glass Filaments, Reinforced Backing with Thermosetting Rubber, Pressure Sensitive Adhesive Data Sheet

High tensile strength High dielectric strength UL recognized Class B (130°C)

3M<sup>™</sup> 46 Electrical Tape is a polyester film/glass filament tape coated with a thermosetting, pressure-sensitive rubber adhesive system. The polyester film/glass backing has excellent physical and electrical characteristics. 46 tape is especially suited for such applications as lead anchoring and banding of coils where high edge-tear resistance and low stretch under application tension are needed.

## Properties Typical Values\* 7.0 mils (.177 mm) Breaking Strength¹ 275 lbs./in (481 N/10 mm) Elongation 5% Adhesion to Steel¹ 50 oz/in (5.4 N/10 mm) Dielectric Strength¹ 5500V Insulation Resistance¹ 3x10³ megohms

1.0 ratio

Test methods: 1 ASTM D-1000

Electrolytic Corrosion Factor<sup>2</sup>

<sup>\*</sup>All values are averages based on several determinations and not intended for specification purposes. Product specifications will be provided upon request.

<sup>&</sup>lt;sup>2</sup> 3M Test Method - available upon request

## Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law

If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set our above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

 $3\mbox{M}$  and Scotchcast are trademarks of the  $3\mbox{M}$  Company. Printed in the UK.

© 3M United Kingdom PLC, 1999

3M United Kingdom PLC Electrical Products Group Hudson Road Bedford MK41 0HR Tel: 01234 268868 Fax: 01234 229433

3M Ireland Electrical products Group 3M House, Adelphi Centre Dun Loaghaire, CO. Dublin, Ireland Tel: (01) 2803555

Fax: (01) 2803509



Jan. 2000