

No.	Murata Global P/N	Size (EIA)	TC Code	Rated Voltage	Cap.	Tol.	QTY
1	GJM0335C1HR20WB01	0201	COG	50Vdc	0.2pF	±0.05pF	20
2	GJM0335C1HR30WB01	0201	COG	50Vdc	0.3pF	±0.05pF	20
3	GJM0335C1HR40WB01	0201	COG	50Vdc	0.4pF	±0.05pF	20
4	GJM0335C1HR50WB01	0201	COG	50Vdc	0.5pF	±0.05pF	20
5	GJM0335C1HR60WB01	0201	COG	50Vdc	0.6pF	±0.05pF	20
6	GJM0335C1HR70WB01	0201	COG	50Vdc	0.7pF	±0.05pF	20
7	GJM0335C1HR80WB01	0201	COG	50Vdc	0.8pF	±0.05pF	20
8	GJM0335C1HR90WB01	0201	COG	50Vdc	0.9pF	±0.05pF	20
9	GJM0335C1H1R0BB01	0201	COG	50Vdc	1.0pF	±0.1pF	20
10	GJM0335C1H1R1BB01	0201	COG	50Vdc	1.1pF	±0.1pF	20
11	GJM0335C1H1R2BB01	0201	COG	50Vdc	1.2pF	±0.1pF	20
12	GJM0335C1H1R3BB01	0201	COG	50Vdc	1.3pF	±0.1pF	20
13	GJM0335C1H1R5BB01	0201	COG	50Vdc	1.5pF	±0.1pF	20
14	GJM0335C1H1R6BB01	0201	COG	50Vdc	1.6pF	±0.1pF	20
15	GJM0335C1H1R8BB01	0201	COG	50Vdc	1.8pF	±0.1pF	20
16	GJM0335C1H2R0BB01	0201	COG	50Vdc	2.0pF	±0.1pF	20
17	GJM0335C1H2R2BB01	0201	COG	50Vdc	2.2pF	±0.1pF	20
18	GJM0335C1H2R4BB01	0201	COG	50Vdc	2.4pF	±0.1pF	20
19	GJM0335C1H2R7BB01	0201	COG	50Vdc	2.7pF	±0.1pF	20
20	GJM0335C1H3R0BB01	0201	COG	50Vdc	3.0pF	±0.1pF	20
21	GJM0335C1H3R3BB01	0201	COG	50Vdc	3.3pF	±0.1pF	20
22	GJM0335C1H3R6BB01	0201	COG	50Vdc	3.6pF	±0.1pF	20
23	GJM0335C1H3R9BB01	0201	COG	50Vdc	3.9pF	±0.1pF	20
24	GJM0335C1H4R0BB01	0201	COG	50Vdc	4.0pF	±0.1pF	20
25	GJM0335C1H4R3BB01	0201	COG	50Vdc	4.3pF	±0.1pF	20
26	GJM0335C1H4R7BB01	0201	COG	50Vdc	4.7pF	±0.1pF	20
27	GJM0335C1H5R0BB01	0201	COG	50Vdc	5.0pF	±0.1pF	20
28	GJM0335C1H5R1CB01	0201	COG	50Vdc	5.1pF	±0.25pF	20
29	GJM0335C1H5R6CB01	0201	COG	50Vdc	5.6pF	±0.25pF	20
30	GJM0335C1H6R0CB01	0201	COG	50Vdc	6.0pF	±0.25pF	20
31	GJM0335C1H6R2CB01	0201	COG	50Vdc	6.2pF	±0.25pF	20
32	GJM0335C1H6R8CB01	0201	COG	50Vdc	6.8pF	±0.25pF	20
33	GJM0335C1E7R0CB01	0201	COG	25Vdc	7.0pF	±0.25pF	20
34	GJM0335C1E7R5CB01	0201	COG	25Vdc	7.5pF	±0.25pF	20
35	GJM0335C1E8R0CB01	0201	COG	25Vdc	8.0pF	±0.25pF	20
36	GJM0335C1E8R2CB01	0201	COG	25Vdc	8.2pF	±0.25pF	20
37	GJM0335C1E9R0CB01	0201	COG	25Vdc	9.0pF	±0.25pF	20
38	GJM0335C1E9R1CB01	0201	COG	25Vdc	9.1pF	±0.25pF	20
39	GJM0335C1E100GB01	0201	COG	25Vdc	10pF	±2%	20
40	GJM0335C1E120GB01	0201	COG	25Vdc	12pF	±2%	20
41	GJM0335C1E150GB01	0201	COG	25Vdc	15pF	±2%	20
42	GJM0335C1E180GB01	0201	COG	25Vdc	18pF	±2%	20
43	GJM0335C1E200GB01	0201	COG	25Vdc	20pF	±2%	20
44	GJM0335C1E220GB01	0201	COG	25Vdc	22pF	±2%	20
45	GJM0335C1E270GB01	0201	COG	25Vdc	27pF	±2%	20
46	GJM0335C1E330GB01	0201	COG	25Vdc	33pF	±2%	20
47	GJM0335C1E110GB01	0201	COG	25Vdc	11pF	±2%	20
48	GJM0335C1E130GB01	0201	COG	25Vdc	13pF	±2%	20
49	GJM0335C1E160GB01	0201	COG	25Vdc	16pF	±2%	20
50	GJM0335C1E240GB01	0201	COG	25Vdc	24pF	±2%	20
51	GJM0335C1E300GB01	0201	COG	25Vdc	30pF	±2%	20