

No.	Murata Global P/N	Size (JIS)	TC Code	Rated Voltage	Cap.	Tol.	QTY
1	GRM0335C1HR10WA01	0201	COG	50Vdc	0.1pF	±0.05pF	20
2	GRM0335C1HR20WA01	0201	COG	50Vdc	0.2pF	±0.05pF	20
3	GRM0335C1HR30WA01	0201	COG	50Vdc	0.3pF	±0.05pF	20
4	GRM0335C1HR40WA01	0201	COG	50Vdc	0.4pF	±0.05pF	20
5	GRM0335C1HR50WA01	0201	COG	50Vdc	0.5pF	±0.05pF	20
6	GRM0335C1HR60WA01	0201	COG	50Vdc	0.6pF	±0.05pF	20
7	GRM0335C1HR70WA01	0201	COG	50Vdc	0.7pF	±0.05pF	20
8	GRM0335C1HR80WA01	0201	COG	50Vdc	0.8pF	±0.05pF	20
9	GRM0335C1HR90WA01	0201	COG	50Vdc	0.9pF	±0.05pF	20
10	GRM0335C1H1R0WA01	0201	COG	50Vdc	1.0pF	±0.05pF	20
11	GRM0335C1H1R1WA01	0201	COG	50Vdc	1.1pF	±0.05pF	20
12	GRM0335C1H1R2WA01	0201	COG	50Vdc	1.2pF	±0.05pF	20
13	GRM0335C1H1R3WA01	0201	COG	50Vdc	1.3pF	±0.05pF	20
14	GRM0335C1H1R5WA01	0201	COG	50Vdc	1.5pF	±0.05pF	20
15	GRM0335C1H1R6WA01	0201	COG	50Vdc	1.6pF	±0.05pF	20
16	GRM0335C1H1R8WA01	0201	COG	50Vdc	1.8pF	±0.05pF	20
17	GRM0335C1H2R0WA01	0201	COG	50Vdc	2.0pF	±0.05pF	20
18	GRM0335C1H2R2WA01	0201	COG	50Vdc	2.2pF	±0.05pF	20
19	GRM0335C1H2R4WA01	0201	COG	50Vdc	2.4pF	±0.05pF	20
20	GRM0335C1H2R7WA01	0201	COG	50Vdc	2.7pF	±0.05pF	20
21	GRM0335C1H3R0WA01	0201	COG	50Vdc	3.0pF	±0.05pF	20
22	GRM0335C1H3R3WA01	0201	COG	50Vdc	3.3pF	±0.05pF	20
23	GRM0335C1H3R6WA01	0201	COG	50Vdc	3.6pF	±0.05pF	20
24	GRM0335C1H3R9WA01	0201	COG	50Vdc	3.9pF	±0.05pF	20
25	GRM0335C1H4R3WA01	0201	COG	50Vdc	4.3pF	±0.05pF	20
26	GRM0335C1H4R7WA01	0201	COG	50Vdc	4.7pF	±0.05pF	20
27	GRM0335C1H5R1WA01	0201	COG	50Vdc	5.1pF	±0.05pF	20
28	GRM0335C1H5R6WA01	0201	COG	50Vdc	5.6pF	±0.05pF	20
29	GRM0335C1H6R2WA01	0201	COG	50Vdc	6.2pF	±0.05pF	20
30	GRM0335C1H6R8WA01	0201	COG	50Vdc	6.8pF	±0.05pF	20
31	GRM0335C1H7R5WA01	0201	COG	50Vdc	7.5pF	±0.05pF	20
32	GRM0335C1H8R2WA01	0201	COG	50Vdc	8.2pF	±0.05pF	20
33	GRM0335C1H9R1WA01	0201	COG	50Vdc	9.1pF	±0.05pF	20
34	GRM0335C1H100GA01	0201	COG	50Vdc	10pF	±2%	20
35	GRM0335C1H120GA01	0201	COG	50Vdc	12pF	±2%	20
36	GRM0335C1H150GA01	0201	COG	50Vdc	15pF	±2%	20
37	GRM0335C1H180GA01	0201	COG	50Vdc	18pF	±2%	20
38	GRM0335C1H220GA01	0201	COG	50Vdc	22pF	±2%	20
39	GRM0335C1H270GA01	0201	COG	50Vdc	27pF	±2%	20
40	GRM0335C1H330GA01	0201	COG	50Vdc	33pF	±2%	20
41	GRM0335C1H390GA01	0201	COG	50Vdc	39pF	±2%	20
42	GRM0335C1H470GA01	0201	COG	50Vdc	47pF	±2%	20
43	GRM0335C1H560GA01	0201	COG	50Vdc	56pF	±2%	20
44	GRM0335C1H680GA01	0201	COG	50Vdc	68pF	±2%	20
45	GRM0335C1H820GA01	0201	COG	50Vdc	82pF	±2%	20
46	GRM0335C1H101GA01	0201	COG	50Vdc	100pF	±2%	20
47	GRM0335C1H121GA01	0201	COG	50Vdc	120pF	±2%	20
48	GRM0335C1H151GA01	0201	COG	50Vdc	150pF	±2%	20
49	GRM0335C1H181GA01	0201	COG	50Vdc	180pF	±2%	20
50	GRM0335C1H221GA01	0201	COG	50Vdc	220pF	±2%	20