


Product Description:

Utilite™ is a powerful yet energy efficient alternative to standard bulkhead utility luminaires. Designed specifically for LED technology, their impact resistant polycarbonate housing provides a tough exterior making them ideal for all basic industrial, commercial and residential installations.

Product Image:**Product Features:**

- IP65 rated polycarbonate housing
- Integrated driver for slim profile
- Wall or ceiling mountable with 20mm knockouts
- Available in a wide range of sizes and shapes to suit multiple installation requirements
- Impact resistant - IK06 rating
- 1.5kV surge protection
- 3 year warranty

15W Polycarbonate IP65 Round LED Bulkhead

Line Drawing Image**Product Specs:**

Technology	LED	Number of LEDs	45
Lifetime L70 (hrs)	25000	Input Voltage	220~240V AC
Input Frequency	50/60HZ	Surge Protection (kV)	1.5
Power Factor	0.5	Dimmable	No
IP Rating	IP65	IK Rating	IK06
Operating Temp. (Max) °C	40	Height (mm)	62
Overall Diameter (mm)	167		

SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-BH115/40	15W	1250lm	83.33	4000K	80	120°	6
EN-BH115/65	15W	1250lm	83.33	6500K	80	120°	6
EN-BH115/30	15W	1200lm	80	3000K	80	120°	6

Compliance & Approvals:



Warranty

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Enlite Sales

16 Alban Park Hatfield Road St. Albans
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21