

Brand Name:	Acer
DVI:	Yes
Environmentally Friendly:	Yes
Green Compliant:	Yes
Number of USB 2.0 Ports:	6
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 7 Professional
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-4460
Processor Speed:	3.20 GHz
Processor Type:	Core i5
Product Family:	Extensa M2610
Product Type:	Desktop Computer
Screen Size:	No
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	6
VGA:	Yes

#### Camera

Screen Size:	No
--------------	----

#### Display & Graphics

Maximum Memory:	16 GB
Screen Size:	No
TV Card:	No

#### General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.X0CEK.016
Manufacturer Website Address:	<a href="http://www.acer.co.uk">http://www.acer.co.uk</a>
Manufacturer:	Acer, Inc
Package Contents:	<ul style="list-style-type: none"><li>• Extensa M2610 Desktop Computer</li><li>• USB Keyboard</li><li>• USB Mouse</li></ul>
Product Line:	Extensa
Product Name:	Extensa M2610 Desktop Computer
Product Series:	M2610
Product Type:	Desktop Computer

#### I/O Expansions

Number of PCI Express x1 Slots:	2
Number of PCI Express x16 Slots:	1
Number of PCI Slots:	1
Number of Total Expansion Slots:	4

#### Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

#### Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
DVI:	Yes
Ethernet Technology:	Gigabit Ethernet
Modem (RJ-11):	No
Modem:	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	6
Total Number of USB Ports:	6
VGA:	Yes

#### Keyboard/Keypad

Keyboard Type:	Physical Keyboard
----------------	-------------------

#### Media & Performance

Ethernet Technology:	Gigabit Ethernet
----------------------	------------------

#### Memory

Maximum Memory:	16 GB
Memory Card Reader:	Yes
Memory Standard:	DDR3-1600/PC3-12800
Memory Technology:	DDR3 SDRAM
Standard Memory:	4 GB

#### Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none"> <li>• DMI</li> <li>• GS</li> <li>• PC2001</li> <li>• CE</li> <li>• CB</li> </ul>
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Green Compliance	RoHS
Certificate/Authority:	
Green Compliant:	Yes
Package Contents:	<ul style="list-style-type: none"> <li>• Extensa M2610 Desktop Computer</li> <li>• USB Keyboard</li> <li>• USB Mouse</li> </ul>
Software Included:	<ul style="list-style-type: none"> <li>• Microsoft® Office Starter: reduced-functionality Word and Excel® only, with advertising. No PowerPoint® or Outlook®. Buy Office 2010 to use the full-featured software.</li> <li>• Bing™ Bar</li> <li>• Windows Live™ Essentials</li> </ul>

#### Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

#### Physical Characteristics

Depth:	372 mm
Height:	365 mm
Width:	175 mm

#### Pointing Device

Pointing Device Type:	Mouse
-----------------------	-------

#### Power Description

Maximum Power Supply Wattage:	220 W
-------------------------------	-------

#### Processor & Chipset

64-bit Processing:	Yes
Cache:	6 MB
Chipset Manufacturer:	Intel
Chipset Model:	H81 Express
Direct Media Interface:	5 GT/s
Hyper-Threading:	No
Maximum Turbo Speed:	3.40 GHz
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Quad-core (4 Core)
Processor Manufacturer:	Intel
Processor Model:	i5-4460
Processor Speed:	3.20 GHz
Processor Type:	Core i5
vPro Technology:	No

#### Product Information

Features:	Security Slot
Operating System Platform:	Windows
Screen Size:	No
Width:	175 mm

#### Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 7 Professional
Software Included:	

- Microsoft® Office Starter: reduced-functionality Word and Excel® only, with advertising. No PowerPoint® or Outlook®. Buy Office 2010 to use the full-featured software.
- Bing™ Bar
- Windows Live™ Essentials

## Storage

Features:	Security Slot
Hard Drive Configuration:	1 x 500 GB
Hard Drive Interface:	Serial ATA/300
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	500 GB

## Technical Information

64-bit Processing:	Yes
Direct Media Interface:	5 GT/s
Ethernet Technology:	Gigabit Ethernet
Features:	Security Slot
Hard Drive RPM:	7200
Memory Card Reader:	Yes
Memory Standard:	DDR3-1600/PC3-12800
Memory Technology:	DDR3 SDRAM
Operating System:	Windows 7 Professional
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Processor Core:	Quad-core (4 Core)
Processor Manufacturer:	Intel
Screen Size:	No

## Wireless Specifications

Features:	Security Slot
-----------	---------------