

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0520300829**
Status: **Active**
Overview: FFC-FPC (Through-Hole)
Description: FFC/FPC Connector, Through-Hole, Vertical, FFC/FPC Connector, ZIF Receptacle, 8 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family FFC/FPC Connectors
Series [52030](#)
Overview [FFC-FPC \(Through-Hole\)](#)
Product Name N/A
UPC 822348168958

Physical

Circuits (Loaded) 8
Contact Position N/A
Durability (mating cycles max) 30
Entry Angle Vertical
Mated Height 5.20mm
Material - Metal Phosphor Bronze
Material - Plating Mating Tin-Bismuth
Material - Plating Termination Tin-Bismuth
Material - Resin Nylon, Polyester
Net Weight 383.401/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 3.20mm
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.00mm
Polarized to PCB No
Stackable No
Temperature Range - Operating -20°C to +80°C
Termination Interface: Style Through Hole
Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 1.0A
Voltage - Maximum 50V

Material Info

Reference - Drawing Numbers

Sales Drawing 520301000, SD-52030-019



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[52030 Series](#)

Mates With

Molex Premo-Flex FFC. Be sure to match like plating