

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0834219044

Status:

Active

Overview:

Commercial Micro-D High-Density Connectors

Description:

Commercial Micro-D, CMD Single Ended, 9 Circuits, Female - Pigtail, 1.83m Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-83422-001 (PDF)

General	
Product Family	Cable Assemblies
Series	83421
Assembly Configuration	Single Ended Connector
Connector to Connector	Commercial Micro-D-to-Pigtail
Overview	Commercial Micro-D High-Density Connectors
Product Name	Commercial Micro-D
UPC	800756424729
Physical	
Cable Length	1.83m
Circuits (Loaded)	9
Gender	Female-Pigtail
Lock to Mating Part	None
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	142.110/g
Packaging Type	Bag
Plating min - Mating	0.127µm
Plating min - Termination	1.270µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	.225mm (5.720") max.
Wire Size AWG	28
Wire/Cable Type	N/A

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-83422-001
Sales Drawing	SD-83421-9023

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

China RoHS

Green Image
Not Relevant

Search Parts in this Series

83421 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION