



Key Features

- Electronic instrument enclosures, ideally suited for mounting printed circuit boards.
- Ergonomically designed for a comfortable fit into the user's hand.
- Designed to meet IP54 ratings.
- Recessed top for membrane display or pad.
- Units with battery door use our long life "three snap" door.
- Lap joint construction provides protection against dust accumulation and splashing water.
- Molded in a choice of black or grey general purpose ABS plastic with a satin texture.
- Translucent Blue version also available [link here](#)
- Unit is secured with self tapping screws.
- Black enclosures include black screws, grey includes nickel finish screws.
- Part numbers 1593NBK, 1593NGY, and 1593NTBU are specifically designed for smart card readers

Some models are designed with a battery door.

Critical Data, No Questions

PDF Data Sheets, 2D AutoCAD, and 3D Models are available for download immediately from our web site.



Accessories

Belt Clip Kits

1599CLIP (black)
1599CLIPGY (gray)



PC Board (some sizes)

1593KPCB (for size "K")
1593LPCB (for size "L")
1593PPCB (for size "P")
1593QPCB (for size "Q")



Infrared Panels

(see table below)



Replacement & Accessory Hardware

(see table below)

Battery Holders

BH1AAWKIT - (1) AAA Cell
BH2AAWKIT - (2) AAA Cells
BH1AAWKIT - (1) AA Cell
BH2AAWKIT - (2) AAA Cells
BS61KIT - (1) 9V Cell



*Compatibility varies

Black	Gray	Trans Blue	Removable Panels	Battery Door	Units	Length	Width	Depth	IR panels (10-pack)	Replacement Assembly Screws (100-pack)	PC Board Screws (100-pack)*
1593KBK	1593KGY	1593KTBU	2	No	Inches mm	2.6 66	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593JBK	1593JGY	1593JTBU	0	No	Inches mm	2.6 66	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593ARBK	1593ARGY	1593ARTBU	2	No	Inches mm	2.95 75	2.91 74	1.06 27	1593ARIR10	1591TS100 (silver) 1591TS100BK (black)	*SC519-50 (50-pack)
1593SBK	1593SGY	1593STBU	1	Yes	Inches mm	3.6 92	2.6 66	0.83 21	1593SIR10	1593MS100 (silver) 1593MS100BK (black)	1593ATS100
1593PBK	1593PGY	1593PTBU	1	Yes	Inches mm	3.6 92	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593LBK	1593LGY	1593LTBU	2	No	Inches mm	3.6 92	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593BBBK	1593BBGY	1593BBTBU	2	No	Inches mm	3.75 95	3 77	1.18 30	1593BBIR10	1591TS100 (silver) 1591TS100BK (black)	1593ATS100
1593NBK	1593NGY	1593NTBU	2	No	Inches mm	4.3 110	2.9 75	1 25	1593NIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593TBK	1593TGY	1593TTBU	1	Yes	Inches mm	4.4 112	2.6 66	0.83 21	1593SIR10	1593MS100 (silver) 1593MS100BK (black)	1593ATS100
1593QBK	1593QGY	1593QTBU	1	Yes	Inches mm	4.4 112	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593DBK	1593DGY	1593DTBU	2	No	Inches mm	4.5 114	1.4 36	1 25	1593DIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593YBK	1593YGY	1593YTBU	1	Yes	Inches mm	5.5 140	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100
1593XBK	1593XGY	1593XTBU	2	No	Inches mm	5.5 140	2.6 66	1.1 28	1593PIR10	1593QS100 (silver) 1593QS100BK (black)	1593ATS100