

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0701070008**
Status: **Active**
Overview: SL™ Modular Connectors
Description: SL™ Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 9 Circuits

Documents:

[3D Model](#) [Packaging Specification PK-70107-100 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70400-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 70107
 Application Signal, Wire-to-Wire
 Comments Version A without Mounting Ears
 Overview [SL™ Modular Connectors](#)
 Product Name SL™
 UPC 800753560833


Physical

Circuits (maximum) 9
 Color - Resin Black
 Flammability 94V-0
 Gender Male
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 1.645/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.54mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40°C to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70107-100
 Product Specification PS-70400-001
 Sales Drawing SD-70107-0001-0024



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[70107](#) Series

Mates With

[70066](#) SL™ Crimp Housing A, G and D
 (Notes: Version C and H will not mate
 to the 70107 housing series), [70400](#)
 SL™ Insulation Displacement Connector
 Assembly, Version G Housing, [70430](#) SL™
 Single Row Receptacle, Version G

Use With

[70021](#) SL™ Crimp Terminal