



## HD 4.30 Black

Available in two variations, the HD 4.30i Black has been optimized for use with Apple products, while the HD 4.30G is fully compatible with Android devices. Both models feature a 3-button remote conveniently located on the cable, which allows to control music and take calls with ease, and the sturdy folding design makes this headset durable and compact enough to be taken anywhere.

- Bass driven acoustics powered by 32 mm Sennheiser proprietary driver
- Soft, comfortable ear pads for enhanced
- High-quality components and carefully selected materials provide many years of reliable use.
- A robust storage pouch protects the headset when not in use.

## **Technical Data**

	UD 4 pg' pl	UD 4 225 PL I
	HD 4.30i Black	HD 4.30G Black
EAN	4044155204698	4044155204681
UPC	615104266933	615104266926
Art. No	506780	506779
General Data		

Frequency response 18-22,000 Hz

Sound pressure level (SPL) 120 dB (1 kHz/1 Vrms)

18 Ω **Impedance** THD - total harmonic distortion < 0.5 %

(1 kHz, 100 dB)

Cable length 1.4m detachable single-sided cable with 3-button remote

Jack plug 3.5mm straight, gold-plated plug for i version / angled for G version

Omnidirectional Pickup pattern Sensitivity (as per 121 TR 9-5) -44 dB V/Pa

**Packaging** 

**Content of delivery** HD 4.30 headset, Storage pouch

Packaging type

Languages on packaging English, German, French, Spanish, Italian, Netherlands and Portuguese

**Dimensions product packaging** 180 x 100 x 260mm

Weight of earphones and packaging 443,0 g

Dimensions of inner master carton (LxBxH)

Number of products in inner NA master carton

Total weight of inner master carton and products

Dimensions of outer master carton

master carton

Total weight of outer master carton and products

393 x 339 x 260mm

Number of products per outer

3,404 g

NA

07/16 Sennheiser is a registered trademark of Sennheiser electronic GmbH & Co. KG www.sennheiser.com