

Notification	
Product Code	NLKVS-558AUDRK
Short Description	450MHz, DDC, 2048 x 1536 Rack Mount
Full Description	The 8 port SVGA splitter can split one input source to up to 8 displays. It can transmit the signal up to 65mtrs and can also be daisy chained for a larger distribution. With a high bandwidth of 450MHz it can duplicate and transmit high quality resolutions up to 2048 x 1536 and can support monitors that are DDC compatible. Please note: If you connect a DDC type monitor to video output port one all other monitors must be able to support the highest resolution of that on port one.
Extra Information	Features: Duplicates input source to up to 8 displays Transmission distance up to 65mtr Supports daisy chaining Supports 450MHz Supports resolution up to 2048 x 1536 DDC compatible Specifications: Input: 15pin VGA female, 3.5mm female Output: 8 x 15pin VGA female and 8x 3.5mm female Supports XGA, VGA, SVGA and Multisync Power consumption: DC5v 200mA(max) Metal housing Dimensions: 268 x 110 x 42mm Contents 8 Port Video Splitter 2 x Rack Mounting Brackets 1 x DC5v 500mA 1 x QIG