

Product Sheet


Part Number: CDSF 18













Family	inserts
Version	spring terminal connections
Series	CDS
Product type	with female contacts
Model	female insert
Reference standard	EN 61984 (2001-11)
Contact type	silver plated
No. of poles	18 poles + 🕒
Voltage (V)	400V
Current (A)	10A (A.C./D.C.)
Wire section	0,14mm² - 2,5mm²
Awg size	26 - 14
Quality mark	% 600V @
IP degree of protection	IP20 degree of protection without enclosure; IP65, IP66, IP67, IP68 (EN 60529) and IP69K (DIN 40050 - 9) with enclosure
Fixing centre distance	size "57.27"
Impulse withstand voltage	6kV
Pollution degree	3

The information and the dimensions contained are not binding and may be changed without prior notice.

The drawing's dimensions are in mm.