

Computer Hardware and Accessories

Monitors and Accessories - cont.

25" Full-HD LED IPS Monitor



Full HD 1080p **NEW** **IPS**
 LikeLife Color Expression

- Model: 25UM65**
- Slimline LED monitor with IPS technology
 - Full-HD 1920x1080 resolution with 21.9 ultra wide aspect ratio
 - Triple Monitor: Three screens to work with three different programs
 - Reader Mode: Reducing blue light to protect your eyes, allows comfortable reading on the monitor for long periods of time
 - Flicker Safe: Protect your eyes from exhausting flickers and blue lights, allowing long periods of time working, gaming or watching movies without burdening your eyes
 - 250cd/m² Brightness
 - 5000000:1 Contrast ratio
 - 178° viewing angle
 - 2x 3W built in speakers
 - DisplayPort, DVI-D and HDMI interface
 - Dimensions (WxDxH): 609x188 4x383mm

Contents: Monitor, UK mains lead and user guide

Order Code	price each
5805451	165.00

SAMSUNG SyncMaster 18.5" HD LED Monitor



HD ready **NEW**

- Model: LS19D300NY**
- Stylish and functional LED monitor
 - HD Ready 1366x768 resolution display
 - Magic Upscale improves image quality
 - Mega dynamic contrast ratio
 - 5ms Response time
 - 200cd/m² Brightness
 - VGA Interface
 - VESA Wall mount compatible (75x75)
 - Dimensions (HxWxD): 348x445x177mm

Contents: Monitor, UK mains lead and user guide

Order Code	price each
5805548	59.95

- 5ms Response time
 - 250cd/m² Brightness
 - Mega dynamic contrast ratio
 - VGA and DVI interfaces
 - VESA Wall mount compatible (100x100)
 - Dimensions (HxWxD): 502x(354-454)x210mm
 - 3 Year manufacturer warranty
- Contents: Monitor, UK mains lead, VGA cable and user guide
- | | |
|----------------|---------------|
| Order Code | price each |
| AV24671 | 109.95 |

pro-SIGNAL Flat Screen Desk Mount



- Model: PSG03904**
- Suitable for 12" to 24" monitors
 - VESA Compatibility: 75 and 100
 - Tilt: ±40°
 - Max. Arm extension: 112.5mm
 - Pivot (Pole / Screen) : 360° / 180°
 - Pole height: 327mm
 - Cable management included
 - Simple installation with mounting hardware included
 - Supplied with desk and grommet mounting clamps
 - Max. Screen weight: 8kg

Order Code	price each
	1+ 3+
ST03361	30.97 29.46

11 27" Full-HD LED IPS Monitor with HDMI



- Model: 27MP3HQ-B**
- Slimline LED-backlit widescreen monitor
 - Consistent, lifelike colours with IPS technology
 - Perfect picture quality without colour shift
 - Flicker-Safe system removes screen flicker
 - 1920x1080 Full-HD display
 - Mega dynamic contrast ratio
 - 5ms Response time
 - 200cd/m² Brightness
 - HDMI and VGA interfaces
 - SUPER Energy Saving mode
 - VESA Wall mount compatible (100x100)
 - Dimensions (HxWxD): 485x42x254mm
 - 1 Year manufacturer warranty

Contents: Monitor, UK mains lead and user guide

Order Code	price each
5805463	139.95

SAMSUNG SyncMaster 19" HD LED Monitor



HD ready **NEW**

- Model: LS19C45KMW**
- Professional, energy efficient LED monitor
 - HAS Design allows you to tailor the monitor height and tilt to meet your exact eye level
 - Innovative Pivot feature allows to rotate the screen up to 90° to match your needs
 - Widescreen 1440x900 WXGA resolution
 - Integrated stereo speakers (2x 1W)
 - 5ms Response time
 - 250cd/m² Brightness
 - VGA and DVI-D interfaces
 - VESA Wall mount compatible (100x100)
 - Dimensions (HxWxD): 423x439x210mm

Contents: Monitor, UK mains lead and user guide

Order Code	price each
5805555	79.95

pro-SIGNAL Flat Screen Desk Mount, Single Arm



- Model: PSG03905**
- Suitable for 12" to 24" monitors
 - VESA Compatibility: 75 and 100
 - Tilt: ±40°
 - Max. Arm extension: 285mm
 - Pivot (Pole / Arm / Screen): 360° / 360° / 180°
 - Pole height: 327mm
 - Integrated cable management
 - Simple installation with mounting hardware included
 - Supplied with desk and grommet mounting clamps
 - Max. Screen weight: 8kg

Order Code	price each
	1+ 3+
ST03362	37.67 35.78

SAMSUNG 22" Series 4 Business LED Monitor



HD ready **NEW**

- Model: LS22C450BW**
- Professional, energy efficient LED monitor
 - HAS Design allows you to tailor the monitor height and tilt to meet your exact eye level
 - Innovative Pivot feature allows to rotate the screen up to 90° to match your needs
 - High definition 1680x1050 resolution display

Easy Online Ordering

Get access to our entire product range - log-on to cpc.co.uk

1050 Fast, easy online ordering at cpc.co.uk