

ARCA 608030S



Sample photo

Order symbol: ARCA 608030S
Product nbr: 8120109
Description: Cabinet, PC
Remarks: Swinghandle

EAN: 6418074085221
EI. number:
Finland: 3424068
Electric No. Denmark: 8212095407

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:		Length	Width	Height	Accessories:		
mm:		600	800	300	MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)	
inch:		23.6	31.5	11.8	MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)	
Materials:					MPX ARCA 8060	Mounting plate (730x530 mm)	
Material:		Polycarbonate			IDS ARCA 6080	Inner door set	
Base colour:		RAL 7035 -light grey			PMK ARCA 80	Pole mounting kit	
Cover colour:		RAL 7035 -light grey			RCS ARCA 6080	Rain canopy set	
Gasket material:		Polyurethane			SBK ARCA 60	Support bar kit	
					SBK ARCA 80	Support bar kit	
Temperatures:					DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060	
Temperature °C (short term):		-40 ... 120 °C			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060	
Temperature °C (continuous):		-40 ... 80 °C					
Temperature °F (short term):		-40 ... 250 °F					
Temperature °F (continuous):		-40 ... 175 °F					
Accessories:							
MPS ARCA 8060		Mounting plate (730x530x2 mm)					
Rating:							
Ingress Protection (EN 60529):		IP66					
Impact Resistance (EN 62262):		IK10 +35°C /IK08 -25°C					
Electrical insulation:		Totally insulated					
Halogen free (DIN/VDE 0472, Part 815):		1					
UV resistance:		UL 508					
Flammability Rating:		UL 94 5VA					
Glow Wire Test (IEC 695-2-1) °C:		960					
Certificates:							
SGS Fimko							
Gost R							

